

KEYING OPTIONS
(SHOWN WITH CPA)

KEYING OPTION: A

SCALE 2:1

KEYING OPTION: B


SCALE 2:1

KEYING OPTION: C

SCALE 2:1

KEYING OPTION: D

SCALE 2:1



- △ 1 CIRCUIT IDENTIFICATION NUMBERS, LOCATED AS SHOWN.
2. SPACER AND CPA ARE SHIPPED IN PRE-ASSEMBLED POSITION.
- △ 3 PART NUMBER, DATE CODE AND WORK CENTER LOCATION .
- △ 4 CAVITY ID.
- △ 5 MATERIAL IDENTIFICATION.
6. PACKING: CONNECTOR ASSEMBLIES BULK PACKAGED IN CARDBOARD BOX.
- △ 7 OPTIONAL SLOTS FOR MOLD CONSTRUCTION.
- △ 8 45° LEAD IN ANGLE OPTIONAL TYPICAL FOR ALL KEYS.
9. SPACER IS SHIPPED IN PRE-LOADED POSITION. SOME SPACERS MAY BECOME FULLY SEATED DURING SHIPPING. USE TE INSTRUCTION SHEET 408-10104 TO REPOSITION SPACER BACK TO IT'S PRE-LOADED POSITION.
10. REFER TO TE INSTRUCTION SHEET 408-8599 FOR PROPER CONTACT ASSEMBLY/DISASSEMBLY AND CONNECTOR MATING/ UN-MATING PROCEDURE.

1456983-8	1456983-7	1456983-6	1456983-5	1456983-4	1456983-3	1456983-2	1456983-1	<----- ASSEMBLY PN			
I	-	I	-	I	-	I	-	CPA	>PBT-GF20<	RED	3
I	I	I	I	I	I	I	I	SPACER	>PBT-GF30<	RED	2
I	I	-	-	-	-	-	-	HOUSING; KEY D	>PA66-GF35<	BLACK	1
-	-	I	I	-	-	-	-	HOUSING; KEY C	>PA66-GF35<	BLACK	
-	-	-	-	I	I	-	-	HOUSING; KEY B	>PA66-GF35<	BLACK	
-	-	-	-	-	-	I	I	HOUSING; KEY A	>PA66-GF35<	BLACK	
QTY REQ'D PER ASSY								DESCRIPTION	MATERIAL	COLOR	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN R. VESTAL	13DEC2006	TE Connectivity	
DIMENSIONS:				CHK D. STRAUSSER	13DEC2006		
mm				APVD D. STRAUSSER	13DEC2006	NAME	
				TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
				0 PLC ±		APPLICATION SPEC	
				1 PLC ±		SIZE	
				2 PLC ±		CAGE CODE	
				3 PLC ±		DRAWING NO	
				4 PLC ±		RESTRICTED TO	
				ANGLES ±		A100779	
MATERIAL				FINISH		C=1456983	
SEE TABLE						SHEET 1 OF 1	
						REV E2	