




MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
130010-0210	113020A01F010	1.00" +.75" -0 [1.3M +19.1 -0]
130010-0214	113020A01F030	3.00' +1.75" -0 [1.9M +44.5 -0]
130010-0221	113020A01F060	6.00' +2.19" -0 [1.8M +55.6 -0]
130010-0226	113020A01F090	9.00' +3.50" -0 [2.7M +88.9 -0]
130010-0228	113020A01F120	12.00' +3.50" -0 [3.7M +88.9 -0]
130010-0233	113020A01F150	15.00' +6.50" -0 [4.6M +165.1 -0]
130010-0238	113020A01F200	20.00' +6.50" -0 [6.1M +165.1 -0]
130010-0241	113020A01F250	25.00' +12.50" -0 [7.6M +317.5 -0]



MALE FACE VIEW



FEMALE FACE VIEW

1	GREEN-YELLOW	1
2	BLACK	2
3	WHITE	3

WIRING DIAGRAM

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PVC	YELLOW
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
4	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED
5	OVERMOLD	PVC	YELLOW
6	CABLE- 16AWG, (65 X #34 COPPER STRANDING), 3 CONDUCTOR, 600V, ST00W, ST	PVC	YELLOW
7	LABEL	MYLAR	BLACK/YELLOW

VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	13 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 105°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

RLSD DRAWING EC NO: WNA2009-0849 DRWN: BWOODMAN 6/10/09 CHKD: ----- APPR: JFMURPHY 2009/07/08	DESCRIPTION	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ----	DESIGN UNITS ----	THIRD ANGLE PROJECTION			
		 =0		mm	INCH	DRAWN BY BW	DATE 2009/03/30	TITLE MINI-CHANGE CORDSET 3 POLE MALE/FEMALE 16 AWG PVC CABLE					
		 =0	4 PLACES	±---	±---	CHECKED BY VO	DATE 2009/03/30						
			3 PLACES	±---	±---	APPROVED BY DATE		molex	MOLEX INCORPORATED				
			2 PLACES	±---	±.01								
			1 PLACE	±0.3	±---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-130010-002		SHEET NO. 1 OF 1			
		ANGULAR ±---°			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											