


Comus Group of Companies

PRODUCT DATA SHEET

PART NUMBER

S1016CW (AG3011-77C)

Manufactured in UK




Drawings not to scale
All dimensions in mm (inches) nominal

These switches operate when tilted from the horizontal position. The switch movement required to cause contact change (example off to on) is called the differential angle. It is very important when designing a tilt switch to allow for the differential angle and understand that when in the horizontal position the switch contact may be open or closed.

SWITCHING VOLTAGE

Unless specified switches can be used on AC and DC loads. For DC voltages reduce AC rating to 70%.



SPECIFICATION

CONTACT FORM/STYLE		See above
SWITCHING VOLTAGE	Max. Vac RMS	120
SWITCHING CURRENT	Max. A	1
SWITCHING CAPACITY	Max. VA	25
DIFFERENTIAL ANGLE	Max. Deg.°	15°
CONTACT RESISTANCE	Max. Ω	3
OPERATING TEMPERATURE	Deg. °C	-20° +70°
STORAGE TEMPERATURE	Deg. °C	-25° +70°
CASE MATERIAL		ABS
CABLE/TERMINATION		2 x 0.52 round silicone rubber insulated. Tag hole 4.3ø (.17)
FEATURES		Rugged Construction

This product is fully sealed to give maximum mechanical protection and minimise the ingress of dust and moisture. As a guide, the product is expected to meet the requirements of IP65.

TILT SWITCH MODULE - Non Mercury Contact

PART NUMBER

S1016CW

Rev. No.	Revision Note	Date	Signature
B	Web Site 2007	02-21-07	LG

The Comus Group of Companies consist of:
Comus International
Comus International BVBA
Comus International SARL
Assemtech Europe Limited
STG India

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.