





DESCRIPTION		
REV.	DATE	
A	07/21/99	REFORMAT DRAWING
B	11/12/99	MODIFY BARREL AND FERRULE DIMENSIONS
C	12/09/03	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTES:
1. CRIMPED FERRULE
HEX. CRIMP SIZE .213"
 2. CRIMPED CONTACT PIN
HEX. CRIMP SIZE .100"

			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.			APPROVALS			Amphenol Connex N CRIMP JACK – CAPTIVE CONTACT (RG 55/U, 142/U, 223/U, 400/U CABLE – 50ohms)		
8			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.			DRAWN	G.R.S.	12/09/03			
7			UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:			CHECKED					
6			0.5 – 8mm ± 0.20mm			ISSUED					
5			8 – 30mm ± 0.40mm			SHEET	1 OF 1				
4	FERRULE	COPPER	NEXCOTE	1		PART NO.			172147		
3	CONTACT PIN	PHOS. BRONZE	GOLD	1		DWG. NO.			172147.DWG		
2	INSULATOR	TEFLON	NATURAL	1		REV.			NC		
1	BODY	BRASS	NEXCOTE	1		SIZE			A		
DESCRIPTION			MATERIAL			FINISH			SCALE		
						QTY			NA		
						DO NOT SCALE DRAWING					