



Technical Data Sheet

5463SURD/S400-A8/MS

Features

- High luminous intensity output
- Oval Shape
- Well defined spatial radiation
- Wide viewing angle ($2\theta_{1/2}$) : $110^\circ / 50^\circ$
- UV resistant epoxy
- Pb free

Descriptions

- This precision optical performance oval LED is specifically designed for passenger information signs
- This lamp has matched radiation patterns with yellow, blue Or green color mixing color applications
- Superior performance in outdoor environment




Applications

- Full color/video signs
- Message boards
- Variable message signs (VMS)
- Commercial outdoor advertising

Device Selection Guide

LED Part No.	Chip		Lens Color
	Material	Emitted Color	
5463SURD/S400-A8/MS	AlGaInP	Hyper red	Red Diffused

Package Dimensions

Notes:

- Other dimensions are in millimeters, tolerance is 0.25mm except being specified.
- Protruded resin under flange is 1.5mm Max LED.
- Bare copper alloy is exposed at tie-bar portion after cutting.

Absolute Maximum Rating ($T_a=25^{\circ}\text{C}$)

Parameter	Symbol	Absolute Maximum Rating	Unit
Forward Current	I_F	50	mA
Pulse Forward Current (Duty 1/10@ 1KHz)	I_{FP}	100	mA
Operating Temperature	T_{opr}	-40 ~ +85	$^{\circ}\text{C}$
Storage Temperature	T_{stg}	-40 ~ +100	$^{\circ}\text{C}$
Electrostatic Discharge	ESD	2000	V
Soldering Temperature	T_{sol}	260 $\pm$ 5	$^{\circ}\text{C}$
Power Dissipation	P_d	115	mW
Reverse Voltage	V_R	5	V

Notes: Soldering time $\leq$ 5 seconds.

Electro-Optical Characteristics (T_a=25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	I _V	360	450	--	mcd	I _F =20mA
Viewing Angle	2 θ _{1/2}	--	X:110Y:50	--	deg	
Peak Wavelength	λ _p	--	632	--	nm	
Dominant Wavelength	λ _d	--	624	--		
Spectrum Half width	Δ λ	--	20	--		
Forward Voltage	V _F	--	2.0	2.3	V	
Reverse Current	I _R	--	--	10	μ A	V _R =5V

Rank Combination (I_F=20mA)

Rank	E	F	G	H
Luminous Intensity	360~450	450~565	565~715	715~900

*Measurement Uncertainty of Luminous Intensity: ±15%

Unit:mcd

Rank	K	L	M
Forward Voltage	1.7~1.9	1.9~2.1	2.1~2.3

*Measurement Uncertainty of Forward Voltage: ±0.1V

Unit:V







Rank	1	2	3
Dominant Wavelength	618~620	620~624	624~628

*Measurement Uncertainty of Dominant Wavelength ±1.0nm

Unit:nm

*The quantity ratio of the ranks is decided by EVERLIGHT.

Typical Electro-Optical Characteristics Curves

Relative Intensity vs. Wavelength

Forward Current vs. Forward Voltage

Relative Intensity vs. Ambient Temp

Forward Current vs. Relative Intensity

Forward Current vs. Ambient Temp.

Radiation Characteristics


Reliability Test Items And Results

No.	Items	Test Condition	Note	Number of Damaged
1	Temperature Cycle	100 °C => 25 °C => -40 °C => 25 °C 15min. 5min. 15min. 5min.	1000cycles	0/22
2	Thermal Shock	100 °C => 25 °C => -10 °C => 25 °C 5min. 10sec. 5min. 10sec.	1000cycles	0/22
3	Steady State Operating life of High Humidity heat	85 °C /R.H85% , I _F =20mA	1000hrs.	0/22
4	Steady State Operating life of High Temperature	T _a =85 °C , I _F =10mA	1000hrs.	0/22
5	Steady State Operating life of Low Temperature	T _a =-40 °C , I _F =10mA	1000hrs.	0/22
6	Steady State Operating life	T _a =25 °C , I _F =50mA	1000hrs.	0/22
7	Soldering heat	Temp.260 °C ±5 °C ,5sec	1 time	0/22

Criteria for Judging the Damage

Item	Symbol	Test Conditions	Criteria for Judgement	
			Min	Max
Forward Voltage	V _F	I _F =20mA	---	U ×1.1
Reverse Current	I _R	V _R =5V	---	U ×2.0
Luminous Intensity	I _V	I _F =20mA	L ×0.7	---

U :Upper Specification limit

L :Lower Specification limit



5463SURD/S400-A8/MS

Packing Quantity Specification

1.500PCS/1Bag, 5Bags/1Box

2.10Boxes/1Carton

Label Form Specification

EVERLIGHT	
CPN:	
P/N:	
	
5463SURD/S400-A8/MS	
QTY :	CAT:
	HUE:
LOT NO :	REF:
	
MADE IN TAIWAN	

CPN: Customer's Production Number

P/N : Production Number

5463SURD/S400-A8/MS:Production name

QTY: Packing Quantity

CAT: Ranks of Luminous and Forward Voltage

HUE: Ranks of Dominant Wavelength

REF: Reference

LOT No: Lot Number

MADE IN TAIWAN: Production Place

Notes

1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD.
Office: No 25, Lane 76, Sec 3, Chung Yang Rd,
Tucheng, Taipei 236, Taiwan, R.O.C

Tel: 886-2-2267-2000, 2267-9936
Fax: 886-2267-6244, 2267-6189, 2267-6306
<http://www.everlight.com>