


LOC		DIST		REVISIONS						
GP	00	P	CTR	DESCRIPTION			DATE	DWN	APVD	
			A	RELEASE PER ECO-05-009687			20SEP2005	DRR	MY	
			B	REVISED PER ECO-05-015421			06DEC2005	DRR	LZ	
			B2	ECR-10-013906			12JUL10	D.S	S.Y	
			B3	ECR-11-013206			27JUN2011	D.P	C.W	

D


C

B

A





- 1 MATERIALS:
- HOUSING: HIGH TEMPERATURE NYLON, BLACK, UL94 V-0
EXTRACTOR: HIGH TEMPERATURE THERMOPLASTIC
CONTACTS: COPPER ALLOY
RETENTION BARB: STAINLESS STEEL
- 2 INTERFACE FINISH:
- (1) 0.00076 MIN THK GOLD OVER 0.00127 MIN THK NICKEL
(2) 0.00038 MIN THK GOLD OVER 0.00127 MIN THK NICKEL
(3) 0.00008 MIN THK GOLD OVER 0.00127 MIN THK NICKEL
- 3 FINISHED HOLE SIZE. 0.15 MAXIMUM ANNULAR RING.
- 4 KEEP OUT ZONE.
- 5 KEEP OUT AREA RESERVED FOR SOCKET EXTRACTORS, BOTH ENDS.
- 6 SOLDER TAIL FINISH:
0.00300 MIN THK BRIGHT TIN-LEAD OVER 0.00127 MIN THK NICKEL.
- 7 SOLDER TAIL FINISH:
0.00300 MIN THK MATTE TIN OVER 0.00127 MIN THK NICKEL.
- 8 LED LOCATION AS APPLICABLE PER CUSTOMER.
- 9 DATUM -G- IS CONNECTOR SIDE SURFACE OF PCB.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	BLACK	7	0.00038 MIN	4.00	2-1761024-4
				3.18	2-1761024-3
	BLACK	7	0.00076 MIN	2.67	2-1761024-2
				4.00	2-1761024-1
SUPERCEDED BY 1-1761024-2		7	0.00008 MIN	3.18	2-1761024-0
				2.67	2-1761024-9
		7	0.00008 MIN	4.00	1-1761024-8
				3.18	1-1761024-7
SUPERCEDED BY 1-1761024-1		7	0.00038 MIN	2.67	1-1761024-6
				4.00	1-1761024-5
		7	0.00076 MIN	3.18	1-1761024-4
				2.67	1-1761024-3
SUPERCEDED BY 1-1761024-0		7	0.00038 MIN	4.00	1-1761024-2
				3.18	1-1761024-1
		7	0.00076 MIN	2.67	1-1761024-0
				4.00	1761024-9
SUPERCEDED BY 1-1761024-2		6	0.00008 MIN	3.18	1761024-8
				2.67	1761024-7
		6	0.00038 MIN	4.00	1761024-6
				3.18	1761024-5
SUPERCEDED BY 1-1761024-1		6	0.00038 MIN	2.67	1761024-4
				4.00	1761024-3
		6	0.00076 MIN	3.18	1761024-2
				2.67	1761024-1
SUPERCEDED BY 1-1761024-0	EXTRACTOR	SOLDER	CONTACT GOLD	TAIL	PART
				LENGTH	NUMBER
	COLOR	TAIL	INTERFACE	2	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN D. RINGLER 11FEB2004		Tyco Electronics Harrisburg, PA 17105-3608	
mm		9 PLC ±.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±.		CHK M. CORRELL 18FEB2004		NAME	
MATERIAL		FINISH		APVD M. YEOMANS 20SEP2005		PRODUCT SPEC	
						108-2214	
						APPLICATION SPEC	
						114-13154	
						WEIGHT	
						A1 00779	
						C=1761024	
						RESTRICTED TO	
						-	
						SCALE 4:1 SHEET 1 OF 3 REV B3	

LOC	DIST	REVISIONS					
GP	00	F	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS TO BE KEPT IN CONFIDENTIALITY AND NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION, NO PART OF THIS DRAWING MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM.		DWN D. RINGLER	11FEB2004	Tyco Electronics Harrisburg, PA 17105-3608							
DIMENSIONS: mm		CHK M. CORRELL	18FEB2004	NAME	SOCKET ASSEMBLY, VERTICAL FB DIMM, SOLDER TAIL, 240 POSITION						
		APVD M. YEOMANS	20SEP2005								
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		SIZE	CAGE CODE						
0 PLC ±.0005 1 PLC ±.005 2 PLC ±.013 3 PLC ±.013 4 PLC ±.0001 ANGLES ±.1°		108-2214 APPLICATION SPEC 114-13154				DRAWING NO	RESTRICTED TO				
MATERIAL	FINISH	WEIGHT	A1 00779 C=1761024 -								
		CUSTOMER DRAWING		SCALE	4:1	SHEET	2	OF	3	REV	B3

