



MARKETING SALES DRAWING
 DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
 DIMENSIONS IN METRIC - []

Electrical Testing
 per Tusonix standard
 test plans and Mil-Std-202
 Test Methods.



NOTES:

- Operating temperature range: -55°C to +125°C.
- Gold plated case and lead.
- Epoxy sealed on opposite end from glass seal.
- Max. recommended soldering temperature: 260°C.
See installation recommendations.
- Recommended mounting hole: .135 dia.
- Solder preform available for mounting.
- Tusonix Standard part number: 4300-021.
Tusonix RoHS compliant part number: 4300-021 LF.
Customer must specify Standard or RoHS part number when ordering.
- RoHS compliant part marked with additional dark green dot for identification.

Cx (pF)	TOL.	DC WORKING VOLTAGE		I.R. MIN. @ 100 (VDC.)	DWV (VDC)	DC CURRENT (AMPS)	MIN. NO LOAD INSERTION LOSS (dB) @ 25° C PER MIL-STD-220					COLOR CODE
		85°C	125°C				1 MHz	10 MHz	100 MHz	1 GHz	10 GHz	
500	GMV	300	200	10 G	500	5	---	----	15	35	40	BROWN

REVISION RECORD		Original Release C.O. 5261		0	VAR5 025, 026, 027 & 1MHz COLUMN ADDED. L.E. 11-07-90 5591 VAR5 681 WAS 030 & VAR 031 ADDED. L.E. 06-10-91 5966 RDN TO COMP FMP. STYLE DWG SPLIT FOR EACH VAR. S.M. 10-02-02 20021001-8-02 ADDED NOTES 7 & 8. S.M. 05-23-05 20050511-2-22
				1	
				2	
				3	
				4	
		--TOLERANCES-- Unless Otherwise Specified		Title SOLDER MOUNT EMI FILTER	
		DECIMAL ± NOTED			
		ANGLES ± 		Drawn S.M. 10-02-02 Scale 5 X	
		TUSONIX TUCSON, ARIZONA		Approved T.C. 10-02-02	
				A	4300-021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4300-021LF](#)