




COIL: @ +25 °C

RESISTANCE 200 OHMS $\pm$ 10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 6.2 VDC

MUST RELEASE

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 50 g's 11 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 3.5 MS MAX

RELEASE 3.0 MS MAX

CONTACT BOUNCE 1 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE
100,000 OPERATIONS

DR. R.B. 8/1/94

CK. 8/1/94



COMMUNICATIONS
INSTRUMENTS, INC.

CUST. P & B

CUST. NO. HCM-11D-12

TYPE "HFW" RELAY

HFW1201S276