

Nominal frequency (f0)

153.6 MHz

Frequency stabilities

Parameter	Frequency stability	Operating temp. range
vs. operating temp. range (df/f@25 °C)	-35 to 35 ppm	-40 ... 85 °C
Parameter	Value	Condition
initial tolerance (df/f)	-20 to 20 ppm	@Vc = 1.65 V; 25 °C
vs. supply voltage change (df/f)	-2.5 to 2.5 ppm	static; 3.3 V ±5 %
vs. load change (df/f)	-1 to 1 ppm	static; Load ± 10 %
vs. aging / year (df/f)	<± 3 ppm	@ 40 °C
vs. aging / 15 years (df/f)	<± 12 ppm	@ 40 °C

Frequency tuning

Parameter	Value	Condition
Electrical frequency control (EFC) (df/f0)	-150 to -50 ppm 50 to 150 ppm	ext. tuning voltage @ 0 V ext. tuning voltage @ 3.3 V
Linearity	< 10 %	
Frequency control input impedance	> 5000 kOhm 30 pF	

RF output

Parameter	Value	Condition
Signal	LVC MOS	
Load	5000 Ohm ±10 % 15 pF ±10 %	
Fan out	3	
Rise Time	< 2.2 ns	@ 20 to 80 %Vout
Fall Time	< 2.2 ns	@ 80 to 20 %Vout
Duty cycle	40 / 60 %	@ 1.65 V
V Low	x < 0.3 V	
V High	x > 2.7 V	
Sub Harmonics	<- 70 dBc	
Spurious	<- 80 dBc	
Enable function	Enable Function Pin 2	output Pin 4
	high	data
	open	data
	low	high tristate

Supply voltage

Parameter	Value	Condition
Supply voltage (Vs)	3.3 V ± 5 %	
Current consumption steady state	< 45 mA	@ Vsnom & 25 °C

Additional Parameters

Parameter	Value	Condition	
Phase Noise	< -65 dBc/Hz	10 Hz	max values
	< -90 dBc/Hz	100 Hz	
	< -120 dBc/Hz	1000 Hz	
	< -130 dBc/Hz	10 kHz	
	< -140 dBc/Hz	100 kHz	
Processing & Packing	handling&processing note		

Additional environmental conditions

Vibration stationary: 9..200Hz, 80m/s ² , sinusoidal
Shock non station. vibrat., incl. shock: 250m/s ² , 6ms
Damp heat operational: temp. range: -10 - +85°C, temp. var.: 2°C/Min, 5-95% RH,
Tensile strength of leads DIN IEC 68 T2-21 (Ua 1)
Flexibility of leads DIN IEC 68 T2-21 (Ub)
Sealing test A nicht dicht (not hermetically sealed)
Solderability DIN IEC 68 T2-20 (Ta) 100% RoHS compliant
Solvent resistance EN 60068-2-45, Test xA non-washable device


Absolute Maximum Ratings

Parameter	Min	Typ	Max	Units	Condition
Operable temperature range	-40		90	°C	
Storage temperature range	-55		125	°C	

Enclosure

Type G218B	Height 5.9 mm
<p style="text-align: center;">G 218</p>	
all units in mm	
<p>Pin Connections</p> <p>Pin 1: Vc (control voltage) Pin 2: Enable / Disable Pin 3: GND(Case) Pin 4: RF-Output Pin 5: N.C. Pin 6: Vs (supply voltage)</p>	
<p>Marking</p> <p>C5310A1-0271 153,600 MHz * VI AYYWW * pin-1 marking</p>	

Reflow profile




Profile Feature	Pb-Free Assembly/Sn-Pb Assembly
Average ramp-up rate (TL to Tp)	3°C/second max.
Preheat -Temperature Min (T _{smin})	150°C
-Temperature Min (T _{smax})	200°C
-Time (min to max) (t _s)	60-180 seconds
T _{smax} to TL - Ramp-up Rate	3°C/second max.
Time maintained above - Temperature (TL)	217°C
- Time (t _L)	60-150 seconds
Peak Temperature (T _p)	max 260°C
Time within 5°C of actual Peak Temperature (t _p)	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

Note: All temperatures refer to topside of the package, measured on the package body surface.

Additional Information

This SMD oscillator has been designed for pick and place reflow soldering.
SMD oscillators must be on the top side of the PCB during the reflow process.

Standard shipping method



Notes:

Unless otherwise stated all values are valid after warm-up time and refer to typical conditions for supply voltage, frequency control voltage, load, temperature (25°C).
Subject to technical modification.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vectron:](#)

[C5310A1-0271](#)