







	1	2	3	4	5	6	7																																																																																						
A	 Dimensions <table><tr><th>Positions</th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>06</td><td>7.62</td><td>5.08</td><td>10.16</td><td rowspan="6">7.62</td></tr><tr><td>08</td><td>10.16</td><td>7.62</td><td>10.16</td></tr><tr><td>14</td><td>17.78</td><td>15.24</td><td>10.16</td></tr><tr><td>16</td><td>20.32</td><td>17.78</td><td>10.16</td></tr><tr><td>18</td><td>22.86</td><td>20.32</td><td>10.16</td></tr><tr><td>20</td><td>25.40</td><td>22.86</td><td>10.16</td></tr></table>  PCB Layout  ① Dimensions <table><tr><th>Positions</th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>24</td><td>30.48</td><td>27.94</td><td>17.78</td><td rowspan="5">15.24</td></tr><tr><td>28</td><td>35.56</td><td>33.02</td><td>17.78</td></tr><tr><td>32</td><td>40.64</td><td>38.10</td><td>17.78</td></tr><tr><td>40</td><td>50.80</td><td>48.26</td><td>17.78</td></tr><tr><td>48</td><td>60.96</td><td>58.42</td><td>17.78</td></tr></table> Material: Contact: Phosphor Bronze thickness 0.15mm Plating: Contact Plating,Tin plated 60u"~80u" Insulator: PBT-4830,UL 94V-0 SPECIFICATIONS: Current Rating:1A Dielectric withstanding Voltage:1000v RMS/minute Insulator resistance:5000 Megohms min. Contact resistance:20 milliohms initial 30 milliohms after test. Operating temperatures:-55°C to 85°C Insertion force:340g(12 oz)>max.per contact. Withdrawal force:80g(2.82 oz)>min.per contact.							Positions	A	B	C	D	06	7.62	5.08	10.16	7.62	08	10.16	7.62	10.16	14	17.78	15.24	10.16	16	20.32	17.78	10.16	18	22.86	20.32	10.16	20	25.40	22.86	10.16	Positions	A	B	C	D	24	30.48	27.94	17.78	15.24	28	35.56	33.02	17.78	32	40.64	38.10	17.78	40	50.80	48.26	17.78	48	60.96	58.42	17.78	A																													
Positions	A	B	C	D																																																																																									
06	7.62	5.08	10.16	7.62																																																																																									
08	10.16	7.62	10.16																																																																																										
14	17.78	15.24	10.16																																																																																										
16	20.32	17.78	10.16																																																																																										
18	22.86	20.32	10.16																																																																																										
20	25.40	22.86	10.16																																																																																										
Positions	A	B	C	D																																																																																									
24	30.48	27.94	17.78	15.24																																																																																									
28	35.56	33.02	17.78																																																																																										
32	40.64	38.10	17.78																																																																																										
40	50.80	48.26	17.78																																																																																										
48	60.96	58.42	17.78																																																																																										
B								B																																																																																					
C								C																																																																																					
D								D																																																																																					
E								E																																																																																					
F								F																																																																																					
G	RoHS compliant Unit: mm <table><tr><td>Scale</td><td>FREE</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td colspan="2">Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>26.05.2014</td><td>Ray</td><td rowspan="4">ASSMANN WSW-No. Axx-LC-TR</td></tr><tr><td>X.</td><td>±0.38</td><td></td><td></td><td></td><td></td><td></td><td rowspan="3">Approved</td><td rowspan="7">29.07.2014</td><td rowspan="3">Amy</td></tr><tr><td>X.X</td><td>±0.25</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.13</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>①</td><td>Update the drawing</td><td>29.07.2014</td><td>Amy</td><td rowspan="3"></td><td colspan="2" rowspan="2">Drawing-No.</td><td colspan="2">ASS 6449 CO</td></tr><tr><td></td><td></td><td>②</td><td>Drawn</td><td>26.05.2014</td><td>Ray</td><td>rev01</td></tr><tr><td>Angle</td><td>±3°</td><td></td><td></td><td></td><td></td><td colspan="3" rowspan="2">Replace</td><td>Sheet</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td colspan="5"></td></tr></table>							Scale	FREE						Date	Name	Customer-No.		TOLERANCE							Drawn	26.05.2014	Ray	ASSMANN WSW-No. Axx-LC-TR	X.	±0.38						Approved	29.07.2014	Amy	X.X	±0.25						X.XX	±0.13						DIM	TOL	①	Update the drawing	29.07.2014	Amy		Drawing-No.		ASS 6449 CO				②	Drawn	26.05.2014	Ray	rev01	Angle	±3°					Replace			Sheet	Angle	TOL	Id.	Modification	Date	Name						G
Scale	FREE						Date	Name	Customer-No.																																																																																				
TOLERANCE							Drawn	26.05.2014	Ray	ASSMANN WSW-No. Axx-LC-TR																																																																																			
X.	±0.38						Approved	29.07.2014	Amy																																																																																				
X.X	±0.25																																																																																												
X.XX	±0.13																																																																																												
DIM	TOL	①	Update the drawing	29.07.2014	Amy		Drawing-No.		ASS 6449 CO																																																																																				
		②	Drawn	26.05.2014	Ray				rev01																																																																																				
Angle	±3°						Replace			Sheet																																																																																			
Angle	TOL	Id.	Modification	Date	Name																																																																																								
H								H																																																																																					