





| REV. | DATE | ECR NO. | DESCRIPTION |
|------|----------|---------|---|
| A | 01/22/04 | - | UPDATE DRAWING FORMAT |
| B | 04/23/08 | 100009 | MODIFY BARREL O.D., FERRULE O.D. AND I.D. |



RECOMMENDED
CABLE STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

| DESCRIPTION | MATERIAL | FINISH | QTY | DO NOT SCALE DRAWING | APPROVALS | DATE | PART DESCRIPTION | | | | | | | |
|-------------|--------------------|-------------|---------|---|-----------|---------------------|------------------|--|------|---|------|---|-------|----|
| 8 | | | | <small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</small> <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:</small> 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:</small> .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" | DRAWN | GRS | 04/23/08 | <h1 style="color: blue; margin: 0;">Amphenol Connex</h1> <p style="margin: 0;">SMA REVERSE POLARITY CRIMP PLUG (FOR RG-174/U, 188A/U, 316/U CABLE)</p> | | | | | | |
| 7 | | | | | CHECKED | | | | | | | | | |
| 6 | | | | | ISSUED | | | | | | | | | |
| 5 | HEAT SHRINK TUBING | | 1 | | SHEET | 1 OF 1 | | PART NO. 132114RP | | | | | | |
| 4 | FERRULE | COPPER | GOLD | | 1 | | | | | | | | | |
| 3 | CONTACT PIN | BER. COPPER | GOLD | 1 | | | DWG. NO. | 132114RP.DWG | REV. | B | SIZE | A | SCALE | NA |
| 2 | INSULATOR | PTFE | NATURAL | 1 | | | | | | | | | | |
| 1 | BODY | BRASS | GOLD | 1 | | | | | | | | | | |
| | | | | | CAD FILE | C:/132/132114RP.DWG | | | | | | | | |