


SURFACE MOUNT .025" SQ POST SOCKET

(2.54 mm) .100" PITCH • SSW SERIES



SSW

Mates:

TSW, MTSW, HTSW,
HMTSW, MTLW, EW, ZW,
TSS, HTSS, ZSS, TSM,
TSSH, DW, HW

SPECIFICATIONS

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over
50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold
-55 °C to +105 °C with Tin

Current Rating (SSW/TSM):

4.7 A per pin
(2 pins powered)

Voltage Rating:

465 VAC/658 VDC

Insertion Depth:

(3.68 mm) .145" to
(6.35 mm) .250"

Max Cycles:

100 with 10 μ " (0.25 μ m) Au

PROCESSING




Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max

SSW	1	NO. PINS PER ROW	22	PLATING OPTION	ROW OPTION	VS	OTHER OPTION
		02 thru 36					
				-F = Gold flash on contact, Matte Tin on tail	-S = Single Row		-XX = Polarized Position
				-L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail	-D = Double Row		-K = -S: (3.50 mm) .138" DIA, -D: (6.50 mm) .256" DIA Polyimide film Pick & Place Pad (03 positions min.)
				-G = 20 μ " (0.51 μ m) Gold on contact, Gold flash on tail			-P = Pick & Place Pad (05 positions min.)
							-TR = Tape & Reel (-02 thru -28)
							-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-02 thru -28)




-P OPTION

ALSO AVAILABLE

Contact Samtec

Other platings

Notch option



Note:

Some lengths, styles and options are non-standard, non-returnable.