


Linear Choke, open version, without socket



Approvals and Compliances

Description

- Linear choke
- Wire leads
- Open version without socket and chassis

Applications

- Smoothing RFI suppression choke
- RFI suppression choke
- Chopper amplifiers
- DC drives and stepper motor controls
- Switching power supplies

Weblinks

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

	to 600 VDC
Rated Current	0.45 - 7 A @ Ta 70 °C
Rated inductance	0.02 - 5 mH, Tol. ±15%
Power Operating Frequency	up to 20 kHz
Terminal Type	Wire leads
Weight	10 - 12 g

Isolation Voltage	2 kV eff., winding to ambient
Climatic Category	40/125/21 acc. to IEC 60068-1
Allowable Operation Temp.	-40 °C to 125 °C

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

Application standards

Application standards where the product can be used


Organization	Design	Standard	Description
 IEC	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment.
 IEC	Designed for applications acc.	IEC 60601-1	Medical electrical equipment - Part 1: General requirements for basic safety and essential performance

Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
 CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
 RoHS	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU
 China RoHS	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
 REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.


Dimension [mm]



Dimensions: see table of variants


Diagrams

Application in DC-DC Converter



1) DC-Input unregulated
2) DC-Output regulated

Derating Curves



Inductance variation as function of the magnetizing current

All Variants

I _n [A]	L _n [mH]	R _{cu} [mΩ]	f _{RES} [MHz]	Inductance drop max [%]	A [mm]	B [mm]	C [mm]	D [mm]	Weight [g]	Packing unit [pcs.]	Order Number
0.45	5	3000	0.3	20	20 mm	15 mm	10 mm		10g	200	DL01-24-0008
0.6	3	1550	0.4	20	20 mm	36 mm	10 mm		11g	200	DL01-24-0007
1.0	1	600	0.8	20	20 mm	15 mm	10 mm		10g	200	DL01-24-0006
1.5	0.5	280	1.3	20	20 mm	15 mm	10 mm		10g	200	DL01-24-0005
1.8	0.3	178	2	20	20 mm	15 mm	10 mm		10g	200	DL01-24-0004

I _n [A]	L _n [mH]	R _{cu} [mΩ]	f _{RES} [MHz]	Inductance drop max [%]	A [mm]	B [mm]	C [mm]	D [mm]	Weight [g]	Packing unit [pcs.]	Order Number
3	0.1	70	8.2	20	20 mm	36 mm	10 mm		10g	200	DL01-24-0003
4.5	0.05	26	8.4	20	20 mm	15 mm	10 mm	0.9 mm	11g	200	DL01-24-0002
7	0.02	12	20.2	20	20 mm	36 mm	10 mm	1.2 mm	12g	150	DL01-24-0001

R_{cu} at T_u 20°C

Inductance drop at I_n

Derating at T_u > 70°C: I = I_n × ((125 - T_u) / 55)^{0.5}

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>