


Specifications switches: Specifications Sealing Boot:

- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations life time
- IP67 sealing
- temperature range:
low temp: -40/+115°C
high temp: -40/+160°C

- Operating temperature:
-40/+85°C
- IP67 sealing
- sealing life time:
2.000.000 operations
- material: silicone



$$H = A + P + 13.2$$

This leaves nominal 0.3 mm clearance between the top of the cap and the inner side of the sealing boot to accomplish assembly tolerances. **A** can be chosen between 10 -13 mm, we recommend 10 mm to reduce building height and optimize cap guidance.

A	P	CAP	H	BUSHING
10.0	1.0	AQCXX-24.2	24.2	AQN-0.5
10.0	2.0	AQCXX-25.2	25.2	AQN-0.5
10.0	3.0	AQCXX-26.2	26.2	AQN-2.5
10.0	4.0	AQCXX-27.2	27.2	AQN-2.5

Cap is available in black (09) or transparent (11).

The dimension H is the overall height of the switch+cap.

Bushing AQN-0.5 accepts panel thickness (P) 0.5-2.5 mm.

Bushing AQN-2.5 accepts panel thickness (P) 2.5-4.0 mm.

Panel cut out $\varnothing$ 12.0 $\pm$ 0.2.

How to order

3 F			+	AQN	-		+	AQC	-		+	AQB01
Switch	Mounting	L 6 low temp. H 9 high temp.		Bushing	Panel			Cap	Overall Height			Sealing boot, incl. sealing ring
	T through-hole S surface mount				0.5 2.5			09 black 11 transparent	24.2 25.2 26.2 27.2			09 black 11 transparent
												

3 F	T			+	AQN	-	.	+	AQC		-	.	+	AQB01	
Switch	Mounting	L 6 low temp. H 9 high temp.	LED		Bushing	Panel			Cap	Overall Height				Sealing boot, incl. sealing ring	
	T through-hole		00 blue			0.5								11 transparent	
			20 green			2.5				24.2					
			40 yellow							25.2					
			60 white							26.2					
			80 red							27.2					
			2040 green/yellow												
			8020 red/green												
			8040 red/yellow												

Keycaps shown on this page can also be used on
illumec™ switch 4F - see page 13

Ordering example: AQB0109 + AQC09-27.2 + AQN-2.5 + 3FTL6

For updates of products and/or changes of specifications please see www.mec.dk