










**Mica wafers**

|                                                                                   |                                                                                   |                                                                                   |                                                                                     |                                                                                     |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  |  |  |  |  |
| <b>art. no.</b><br><b>GS 220 C</b><br>TO 220                                      | <b>art. no.</b><br><b>GS 218</b><br>TO 218                                        | <b>art. no.</b><br><b>GS 3 P SL</b><br>TOP 3                                      | <b>art. no.</b><br><b>GS 66 P</b><br>TO 66                                          | <b>art. no.</b><br><b>GS 220 4</b><br>TO 220                                        |
|  |  |  |   |                                                                                     |
| <b>art. no.</b><br><b>GS 220 P</b><br>TO 220                                      | <b>art. no.</b><br><b>GS 32 P</b><br>SOT 32                                       | <b>art. no.</b><br><b>GS 3 P</b><br>TOP 3                                         | <b>art. no.</b><br><b>GS 3</b><br>TO 3                                              |                                                                                     |

|                                  | <b>GS</b>                                |
|----------------------------------|------------------------------------------|
| <b>material</b>                  | muskovit                                 |
| <b>material thickness</b>        | 0.05 mm                                  |
| <b>thermal resistance (GS 3)</b> | 0.4 K/W                                  |
| <b>insulation resistance</b>     | $3 \cdot 10^{17} \Omega \cdot \text{cm}$ |
| <b>snap through stability</b>    | 5 kV                                     |