


LOC	DIST	REVISIONS				
G	86	P	LTR	DESCRIPTION	DATE	APVD
			F	REV PER 0G3A-0637-01	030CT02	JRMS

- 1TIN PLATE 0.00381 [0.000150] MIN THK PER ASTM B 545
- 2CLEANED, UNPLATED
- 3PREPRODUCTION - FASR REQ.



2-	31-324447-0
1-	324447
FINISH	AMP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM01JUL96	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK WJ VOCKROTH02JUL96			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	APVD JL MECKLEY02JUL96	NAME WIRE SPLICE, PARALLEL, AMPOWER™ WIRE SIZE: 250 MCM		
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL COPPER PER ASTM B-75 ANNEALED	FINISH SEE TABLE	WEIGHT .042 lbs	SIZE A3	CAGE CODE 00779	DRAWING NO C-324447
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1	REV F