




Dimensions: mm (In.)

**Electrical Specifications:**

- Max. Switch Rating: <6mA/24VDC
- Electrical Life Endurance: >50,000 cycles
- Contact Resistance: 2Ω max. (measured at 45° tilt)

Mechanical Specifications:

- Differential Angle: 30° max.
- Operating Temperature: 0°~+100°C

Soldering Process:

- Temperature: 250°C, 3 seconds
(Can be soldered by hand only.)

Materials:

- Switch Housing: Copper coated with gold (10μ)
- Terminal: Copper coated with gold
- Rolling Ball: Copper coated with gold. Ball weighted 0.25g.

Note:

- RoHS Compliant

Rolling-Ball Tilt Switch
107-2010-EV

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[107-2010-EV](#)