




1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. MATERIAL: HOUSING & COVER - POLYPHENYLENE OXIDE (BLACK)
TERMINALS - GOLD OVER NICKEL PLATED
HIGH STRENGTH COPPER ALLOY ON
MATING FACE & GOLD FLASH OVER NICKEL
PLATE ON TERMINATING SIDE.
EMI SHIELD - NICKEL PLATED DIE CASTING.


3. COVER SHOWN LOOSE BUT SHIPPED ASSEMBLED.
4. WIRE RANGE: 26 AWG SOLID THRU 30 AWG SOLID
AND 28 AWG STRANDED RIBBON CABLE.

5. FLAT CABLE SHALL BE FURNISHED BY CUSTOMER.
6. MATING FACE CONSISTS OF TWO ROWS OF TERMINALS
ON .085 CENTERS. TERMINATING SIDE CONSISTS OF
TERMINALS ON .100 CENTERS FOR AN EFFECTIVE
.050 TERMINATION.

7. PANEL THICKNESS RANGE: OUTSIDE MOUNTING-.125 MAX.
INSIDE MOUNTING-.062 MAX.

8. EMI SHIELD SHIPPED LOOSE.


9. FOR MORE INFORMATION REFER TO AMP PRODUCT
SPECIFICATION 108-6076 & APPLICATION SPEC
114-6030.



DIM. D	DIM. C	DIM. B	DIM. A	DESCRIPTION
.620	.310	.149	2.085	REAR PANEL MOUNTING
.640	.320	.126	2.000	FRONT PANEL MOUNTING

△ SUGGESTED PANEL CUTOUT

554348-1 AS SHOWN



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.	
TOLERANCES ON:	
DECIMALS ± .005	
ANGLES	
MATERIAL	△
FINISH	△
CONTRACT NO	
DR M. St. Budy 12/9/83	
CHK M. St. Budy 12-29-83	
APPD M. St. Budy 1/13/84	
APPD M. St. Budy 1/13/84	
DSGN APPD	
OTHER APPD	
NAME	
AMP AMP INCORPORATED Harrisburg, Pa. 17105	
EMI RECEPTACLE ASSEMBLY, 36 POSITION, LOW PROFILE, SHIELDED, CHAMP LATCH	
SIZE	FSM NO
C	00779
DRAWING NO	554348
SCALE 2:1	SHEET 1 OF 1

CUSTOMER DRAWING