




P	LTR	DESCRIPTION	DATE	DWN	APVD
Z		REVISED PER ECO-16-016569	23JAN2017	SY	SY



- 1 HOUSING: GLASS FILLED POLYESTER; COLOR: BLACK.
- 2 CONTACT: PHOSPHOR BRONZE.
- 3 NICKEL UNDERPLATE: 0.00127 [0.000050] MIN - ALL OVER.
- 4 TIN-LEAD PLATE: 0.00254 [0.000100] MIN - SOLDER POSTS.
- 5 GOLD PLATE: 0.00076 [0.000030] MIN - CONTACT AREA.
- 6 NICKEL PLATE PER MIL-G-45204. GOLD PLATE PER QQ-N-290.
- 7 PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE AREA SHOWN, EITHER SIDE.
- 8 RECOMMENDED PCB FINISHED HOLE DIA: 1.02 ± 0.08 [0.040 ± 0.003].
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: R.SHIREY/UTA 11/5/91		STE TE Connectivity	
DIMENSIONS: MM[INCHES]		CHK: J.DIORAZIO 8-10-92		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: J.DIORAZIO 8-10-92		SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO	
0 PLC ± -		PRODUCT SPEC		A100779C=530844	
1 PLC ± -		108-9039		—	
2 PLC ± -		APPLICATION SPEC		—	
3 PLC ± 0.13 [0.005]		—		—	
4 PLC ± -		WEIGHT: 0		—	
ANGLES ± -		CUSTOMER DRAWING		—	
MATERIAL: HOUSING: 1 CONTACT: 2		SCALE: 5:1		SHEET 1 OF 2 REV Z	

