Ceramic Disc Capacitors
Class 1 and 2, 100 V (DC) General Purpose

FEATURES

- Low losses
- High stability
- High capacitance in small size
- Kinked (preferred) or straight leads.
- Lead (Pb)-free available.

APPLICATIONS

- Bypassing
- Coupling
- Resonant circuit.

DESIGN

The capacitors consist of a ceramic disc both sides of which are silver-plated. Connection leads are made of tinned copper having a diameter of 0.6 mm.

The capacitors have inward kinked leads with a spacing of 5 mm (0.200") and a lead length from 4 to 30 mm. Encapsulation is made of phenolic resin.



Capacitors with 5 mm (0.20") lead spacing.

CAPACITANCE RANGE:

Class 1, at 1 MHz, 1.2 V (RMS); 1.0 to 100 pF
1 kHz, 1 ± 0.2V (RMS) for capacitance values higher than 1000 pF.

Class 2, at 1 kHz, 1 ± 0.2 V (RMS); 150 to 47000 pF

RATED DC VOLTAGE:

100 V

DIELECTRIC STRENGTH:

250 % of rated voltage

INSULATION RESISTANCE AT 100V (DC):

≥ 10000 MΩ

TOLERANCE ON CAPACITANCE:

± 0.25 pF; ± 0.5 pF; ± 5 % ; ± 10 %; ± 20 %; + 80 /- 20 %

DISSIPATION FACTOR:

Class 1, C ≤ 30 pF; ≤ 20 x (10/C + 0.7) x 10^{-4} maximum

Class 1, C > 30 pF; ≤ 20 x 10^{-4}

Class 2, ≤ 3.0 %

TEMPERATURE COEFFICIENTS:

Class 1 NP0; SL0

Class 2 Y5P; Z5U; Y5V; Z5V

SECTIONAL SPECIFICATIONS:

Class 1 IEC 60 384-8,

Class 2 IEC 60 384-9,

EIA 198

CLIMATIC CATEGORY:

Class 1 55/125/21

Class 2 10/85/21 and 30/85/21

OPERATING TEMPERATURE RANGE:

Class 1 - 55 to + 125 °C

Class 2 - 30 to + 85 °C

MARKING

Marking indicates capacitance value and tolerance in accordance with *"EIA 198"*.

The capacitors meet the essential requirements of "EIA 198". Unless stated otherwise all electrical values apply at an ambient temperature of 25 ± 3 °C, at normal atmospheric conditions

ORDERING INFORMATION, CLASS 1, 100 V (DC), KINKED

C (pF)	TOL. (%)	D_{max} (mm)	LEAD SPACING F (mm)	SH[2] (mm)	CLEAR TEXT CODE: 13th DIGIT: T = REEL; U = AMMO; 3 = BULK; 16th DIGIT: R = RoHS COMPLIANT	PACKAGING CODE 8th AND 9th DIGIT[3]: REEL	AMMO	BULK	CATALOG NUMBER[4] 3rd DIGIT: 5 = STANDARD 8 = RoHS COMPLIANT
CLASS 1 NP0									
1.0	± 0.25 pF	5.0	5.0	4.0	D109C20C0KH6.J5.	06	08	10	22.2 506 ..044
1.5					D159C20C0KH6.J5.				22.2 506 ..144
2.2					D229C20C0KH6.J5.				22.2 506 ..244
3.3					D339C20C0KH6.J5.				22.2 506 ..344
4.7					D479C20C0KH6.J5.				22.2 506 ..444
6.8	± 0.5 pF				D689D20C0HH6.J5.				22.2 506 ..645
10	± 5				D100J20C0GH6.J5.				22.2 506 ..005
12					D120J20C0GH6.J5.				22.2 506 ..055
15					D150J20C0GH6.J5.				22.2 506 ..105
18					D180J20C0GH6.J5.				22.2 506 ..155
22					D220J20C0GH6.J5.				22.2 506 ..205
27					D270J20C0GH6.J5.				22.2 506 ..255
33					D330J20C0GH6.J5.				22.2 506 ..305
39		6.5			D390J25C0GH6.J5.				22.2 506 ..355
47					D470J25C0GH6.J5.				22.2 506 ..405
CLASS 1 SL0									
56	± 5	5.0	5.0	4.0	D560J20SL0H6.J5.	06	08	10	22.2 566 ..505
68					D680J20SL0H6.J5.				22.2 566 ..605
82					D820J20SL0H6.J5.				22.2 566 ..805
100					D101J20SL0H6.J5.				22.2 566 ..015

Notes

1. Maximum thickness 4.0 mm.
2. SH = seated height.
3. Packaging codes refer to inward kinked leads. Other styles available on request.
4. 3rd digit to complete RoHS catalog number. 8th and 9th digit of the catalog number to be completed with the packaging code.

ORDERING INFORMATION, CLASS 2, 100 V (DC), KINKED

C (pF)	TOL. (%)	D_{max} (mm)	LEAD SPACING F (mm)	SH[2] (mm)	CLEAR TEXT CODE: 13th DIGIT: T = REEL; U = AMMO; 3 = BULK; 16th DIGIT: R = RoHS COMPLIANT	PACKAGING CODE 8th AND 9th DIGIT[3]: REEL	AMMO	BULK	CATALOG NUMBER[4] 3rd DIGIT: 5 = STANDARD 8 = RoHS COMPLIANT
CLASS 2 Y5P									
150	± 10	5.0	5.0	4.0	D151K20Y5PH6.J5.	06	08	10	22.2 616 ..111
180					D181K20Y5PH6.J5.				22.2 616 ..161
220					D221K20Y5PH6.J5.				22.2 616 ..211
330					D331K20Y5PH6.J5.				22.2 616 ..311
470					D471K20Y5PH6.J5.				22.2 616 ..411
680					D681K20Y5PH6.J5.				22.2 616 ..611
1000					D102K20Y5PH6.J5.				22.2 616 ..021
1500		6.5			D152K25Y5PH6.J5.				22.2 616 ..121
1800					D182K25Y5PH6.J5.				22.2 616 ..171
2200					D222K25Y5PH6.J5.				22.2 616 ..221
3300		7.5			D332K29Y5PH6.J5.				22.2 616 ..321
4700		8.5			D472K33Y5PH6.J5.				22.2 616 ..421
6800		10.0			D682K39Y5PH6.J5.				22.2 616 ..621
10000		11.0			D103K43Y5PH6.J5.				22.2 616 ..031

ORDERING INFORMATION, CLASS 2, 100 V (DC), KINKED

C (pF)	TOL. (%)	D_{max} (mm)	LEAD SPACING F (mm)	SH[2] (mm)	CLEAR TEXT CODE: 13th DIGIT: T = REEL; U = AMMO; 3 = BULK; 16th DIGIT: R = RoHS COMPLIANT	PACKAGING CODE 8th AND 9th DIGIT[3]: REEL	AMMO	BULK	CATALOG NUMBER[4] 3rd DIGIT: 5 = STANDARD 8 = RoHS COMPLIANT
CLASS 2 Z5U									
1000	± 20	5.0	5.0	4.0	D102M20Z5UH6.J5.	06	08	10	22.2 646 ..022
1500					D152M20Z5UH6.J5.				22.2 646 ..122
2200					D222M20Z5UH6.J5.				22.2 646 ..222
3300					D332M20Z5UH6.J5.				22.2 646 ..322
4700		6.5			D472M25Z5UH6.J5.				22.2 646 ..422
6800					D682M25Z5UH6.J5.				22.2 646 ..622
10000		7.5			D103M29Z5UH6.J5.				22.2 646 ..032
15000		8.5			D153M33Z5UH6.J5.				22.2 646 ..132
22000		10.0			D223M39Z5UH6.J5.				22.2 646 ..232
CLASS 2 Y5V									
1000	+ 80/– 20 %	5.0	5.0	4.0	D102Z20Y5VH6.J5.	06	08	10	22.2 636 ..023
1500					D152Z20Y5VH6.J5.				22.2 636 ..123
2200					D222Z20Y5VH6.J5.				22.2 636 ..223
3300					D322Z20Y5VH6.J5.				22.2 636 ..323
4700		6.5			D472Z20Y5VH6.J5.				22.2 636 ..423
6800					D682Z25Y5VH6.J5.				22.2 636 ..623
10000		7.5			D103Z29Y5VH6.J5.				22.2 636 ..033
15000		8.5			D153Z33Y5VH6.J5.				22.2 636 ..133
22000		10.0			D223Z39Y5VH6.J5.				22.2 636 ..233
CLASS 2 Z5V									
4700	+ 80/– 20 %	5.0	5.0	4.0	D472Z20Z5VH6.J5.	06	08	10	22.2 656 ..423
10000		6.5			D103Z25Z5VH6.J5.				22.2 656 ..033
22000		8.5			D223Z33Z5VH6.J5.				22.2 656 ..233
47000		11.0			D473Z43Z5VH6.J5.				22.2 656 ..433

Notes

1. Maximum thickness 4.0 mm.
2. SH = seated height.
3. Packaging codes refer to inward kinked leads. Other styles available on request.
4. 3rd digit to complete RoHS catalog number. 8th and 9th digit of the catalog number to be completed with the packaging code.

PACKAGING

D_{max} (mm)	SIZE CODE	PACKAGING QUANTITIES: BULK	REEL	AMMO
5.0 (0.20")	20	1000	2500	2000
6.5 (0.25")	25			
7.5 (0.29")	29			
8.5 (0.33")	33			
10.0 (0.39")	39			
11.0 (0.43")	43			

Note

1. The capacitors are supplied in bulk packaging (cardboard boxes), in tape on reel or in ammopack.



Kinked capacitors on tape, lead spacing 5.0 mm (0.2”), on tape.

DIMENSIONS OF TAPE			
SYMBOL	PARAMETER	DIMENSIONS (mm)	
		NOMINAL	TOLERANCE
D	body diameter	11.0 maximum	-
d	lead diameter	0.6	± 0.05
P	pitch between capacitors	12.7	± 1.0
P_0	feed-hole pitch	12.7	± 0.3; note 1
ΔP	plane deviation	1.0 maximum	-
P_1	feed-hole centre to lead centre	3.85	± 0.7; note 2
P_2	feed-hole centre to component centre	6.35	± 1.3; note 2
F	lead spacing	5.0	+ 0.6 - 0.4
Δh	component alignment	0	± 1.0
Δs	deviation along tape, left or right	0	± 1.0
W	tape width	18.0	+ 1.0 - 0.5
W_0	hold-down tape width	5.0 minimum	-
W_1	hole position	9.0	+ 0.75 - 0.5
W_2	hold-down tape margin	3.0 maximum	-
H_0	height to seating plane	16.0	± 0.5
H_1	maximum component height	32.0	-
e	lead end protrusion	1.0 maximum	-
L	maximum length of snipped lead	11.0	-
D_0	feed-hole diameter	4.0	± 0.2
t	total tape thickness	0.9 maximum	–
t_1	maximum thickness of tape and wires	1.5 maximum	–

Notes

1. Cumulative pitch error: ± ≤ 1 mm /20 pitches.
2. Obliquity maximum 3°.

REEL AND TAPE DATA in millimeters



Reel with capacitors on tape.



Ammopack with capacitors on tape.

Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.