


BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD



ATS Part#: **ATS-50425P-C1-R0**
Description: 42.50 x 42.50 x 17.50 mm BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD

Heat Sink Type: **maxiFLOW**
Heat Sink Attachment: **maxiGRIP**
Equivalent Part Number: **ATS-50425P-C2-R0**

**Image above is for illustration purpose only.*

Features & Benefits

- **maxiFLOW™** design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- **maxiGRIP™** attachment applies steady, even pressure to the component and does not require holes in the PCB
- Meets Telcordia GR-63-Core Office Vibration; ETSI 300 019 Transportation Vibration; and MIL-STD-810 Shock and Unpackaged Drop Testing standards
- Comes preassembled with high performance thermal interface material
- Designed for standard height components from 3 to 4.5mm

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	1.9 °C/W	1.5 °C/W	1.3 °C/W	1.2 °C/W	1.1 °C/W	1 °C/W	1 °C/W
	Ducted Flow	1.5	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	42.50 mm	42.50 mm	17.50 mm	72.9 mm	T412	BLUE-ANODIZED
Notes: • Dimension A and B refer to component size. • Dimension C is the heat sink height from the bottom of the base to the top of the fin field. • ATS-50425P-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint-Gobain C675). • Thermal performance data are provided for reference only. Actual performance may vary by application. • ATS reserves the right to update or change its products without notice to improve the design or performance. • ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. • Optional maxiGRIP™ Installation/Removal Tool Set P/N: MGT170 • Contact ATS to learn about custom options available.						

**Image above is for illustration purpose only.*