FC




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW




SECTION Y-Y

mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		scale 4:1 FCI	title RIBCAGE III T/M VERT. HEADER ASS'Y		
T					angles	linear				
					0.02	.XX±.01/0.3 .XXX±.005/0.13 .XXXX±.0020/0.051				
					dr	M. CORNMAN 6/6/95		dwg no	sheet 2 of 6	size
					enr	D. WHITING 6/6/95			95776	A3
					chr	D. WHITING 6/6/95				
					appd	D. WHITING 6/6/95				
sheet index	revision sheet									


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS


STYLE
1





STYLE
2




STYLE
4



STYLE
6



STYLE
7




mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title			
T					angles	linear	.XX±.01/0.3	INCH/MM ↔	RIBCAGE III T/M VERT. HEADER ASS'Y				
					.XXX±.005/0.13								
				0氣2?	.XXXX±.0020/0.051								
					dr	M. CORNMAN	6/6/95		dwg no		sheet3 of 6		size
					engr	D. WHITING	6/6/95		95776		A3		
					chr	D. WHITING	6/6/95						
					appd	D. WHITING	6/6/95		type Product Customer Drawing				
sheet index		revision sheet											


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2




STYLE
4



STYLE
6



STYLE
7




mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
					0.002?		VERT. HEADER ASS'Y		
					dr	M. CORNMAN	6/6/95	dwg no	sheet 4 of 6
					enr	D. WHITING	6/6/95	95776	A3
					chr	D. WHITING	6/6/95	type Product Customer Drawing	
					appd	D. WHITING	6/6/95		
sheet	revision								
index	sheet								


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
					0.002?		VERT. HEADER ASS'Y		
							dwg no		
					dr	M. CORNMANN	6/6/95	sheet 5 of 6	size
					enrg	D. WHITING	6/6/95	95776	A3
					chr	D. WHITING	6/6/95	type	
					appd	D. WHITING	6/6/95	Product Customer Drawing	
sheet	revision								
index	sheet								

