

MMBT918W

VHF/UHF NPN SILICON TRANSISTOR

VOLTAGE 15 Volts **POWER** 225 mWatts


SOT-323 Unit: inch (mm)

FEATURES

- NPN silicon
- Lead free in comply with EU RoHS 2002/95/EC directives.
- Green molding compound as per IEC61249 Std. . (Halogen Free)

MECHANICAL DATA

- Case: SOT-323, Plastic
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 5 mg
- Marking: R1B



ABSOLUTE RATINGS

PARAMETER	Symbol	Value	Units
Collector - Emitter Voltage	V_{CEO}	15	V
Collector - Base Voltage	V_{CBO}	30	V
Emitter - Base Voltage	V_{EBO}	3.0	V
Collector Current - Continuous	I_C	50	mA

THERMAL CHARACTERISTICS

PARAMETER	Symbol	Value	Units
Total Device Dissipation (Note1) $T_A=25^{\circ}C$ Derate above $25^{\circ}C$	P_D	225 1.8	mW mW/ $^{\circ}C$
Thermal Resistance , Junction to Ambient	$R_{\theta JA}$	556	$^{\circ}C/W$
Junction and Storage Temperature	T_J, T_{STG}	-55 to 150	$^{\circ}C$

Note 1: FR.4 = 70 x 60 x 1mm.

MMBT918W

ELECTRICAL CHARACTERISTICS

Characteristic	Symbol	Test Condition	MIN.	MAX.	Units
OFF CHARACTERISTICS					
Collector - Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C=3.0mA, I_B=0$	15	-	V
Collector - Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C=1.0\mu A, I_E=0$	30	-	V
Emitter - Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E=10\mu A, I_C=0$	3.0	-	V
Collector Cutoff Current	I_{CBO}	$V_{CB}=15V, I_E=0$	-	50	nA
ON CHARACTERISTICS					
DC Current Gain	h_{FE}	$I_C=3.0mA, V_{CE}=1.0V$	20	-	-
Collector - Emitter Saturation Voltage	$V_{CE(SAT)}$	$I_C=10mA, I_B=1.0mA$	-	0.4	V
Base - Emitter Saturation Voltage	$V_{BE(SAT)}$	$I_C=10mA, I_B=1.0mA$	-	1.0	V
SMALL-SIGNAL CHARACTERISTICS					
Current Gain Bandwidth Product	f_T	$I_C=4.0mA, V_{CE}=10V, f=100MHz$	600	-	MHz
Output Capacitance	C_{obo}	$V_{CB}=0V, I_E=0, f=1.0MHz$ $V_{CB}=10V, I_E=0, f=1.0MHz$	- -	3.0 1.7	pF
Input Capacitance	C_{ibo}	$V_{EB}=0.5V, I_C=0, f=1.0MHz$	-	2.0	pF





Fig.34

MMBT918W

MOUNTING PAD LAYOUT



ORDER INFORMATION

- Packing information
 - T/R - 12K per 13" plastic Reel
 - T/R - 3K per 7" plastic Reel



MMBT918W

Part No_packing code_Version

MMBT918W_R1_00001

MMBT918W_R2_00001

For example :

RB500V-40_R2_00001

Part No.

Serial number

Version code means HF

Packing size code means 13"

Packing type means T/R

Packing Code XX				Version Code XXXXX		
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number
Bulk Packing (B/P)	B	13"	2			
Tube Packing (T/P)	T	26mm	X			
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y			
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U			
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D			



MMBT918W

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.