


MODEL 72

3/8" Square

Single Turn

Cermet Trimming

Potentiometer



ELECTRICAL

Standard Resistance Range, Ohms	10 to 2Meg
Standard Resistance Tolerance	$\pm 10\%$ (<100 Ohms = $\pm 20\%$)
Input Voltage, Maximum	200 Vdc or rms not to exceed power rating
Slider Current, Maximum	100mA or within rated power, whichever is less
Power Rating, Watts	0.5 at 85°C derating to 0 at 125°C
End Resistance, Maximum	2 Ohms
Actual Electrical Travel, Nominal	244°
Dielectric Strength	900 Vrms
Insulation Resistance, Minimum	1,000 Megohms
Resolution	Essentially infinite
Contact Resistance Variation, Maximum	1% or 1 Ohm, whichever is greater

ENVIRONMENTAL

Seal	85°C Fluorinert® (No Leaks)
Temperature Coefficient, Maximum	$\pm 100\text{ppm}/^\circ\text{C}$
Operating Temperature Range	-55°C to +125°C
Thermal Shock	5 cycles, -55°C to +125°C (1% Δ RT, 1% Δ VR)
Moisture Resistance	Ten 24 hour cycles (1% Δ RT, IR 100 Megohms Min.)
Shock, 6ms Sawtooth	100G's (1% Δ RT, 1% Δ VR)
Vibration	20G's, 10 to 2,000 Hz (1% Δ RT, 1% Δ VR)
High Temperature Exposure	250 hours at 125°C (2% Δ RT, 2% Δ VR)
Rotational Life	200 cycles (3% Δ RT)
Load Life at 0.5 Watts	1,000 hours at 70°C (2% Δ RT)
Resistance to Solder Heat	260°C for 10 sec. (1% Δ RT)


MECHANICAL

Mechanical Stops	Solid
Torque, Starting Maximum	3 oz.-in. (0.021 N-m)
Weight, Nominal	.025 oz. (0.70 grams)

Fluorinert® is a registered trademark of 3M Company.
Specifications subject to change without notice.


TOP ADJUSTMENT (Inch/mm)

Model 72P




Note: Model 72P dimensions applicable to all other models except as noted


Model 72PL



Model 72PM




Model 72PX, 72RPX



Model 72RPX - Terminals 1 and 3 are reversed

Model 72RP



Model 72RX - Terminals 1 and 3 are reversed


Model 72RXL And 72RW - Terminals 1 and 3 are reversed

Model 72RXW - Terminals 1 and 3 are reversed

EXTENDED ROTOR OPTION (Inch/mm)

Available for all Model 72 pin styles:

72PE, 72PLE, 72PME, 72PXE, 72RPXE, 72XE, 72RXE,
72XLE, 72RXLE, 72RWE, 72XWE, 72RXWE




ADJUSTMENT KNOB OPTION (Inch/mm)

Available options:

72XT- Side Adjustment (See 72X for Pin Configuration)

72PT- Top Adjustment (See 72P for Pin Configuration)



72PT Shown - Dimensions applicable to 72XT

STANDARD RESISTANCE VALUES, OHMS

10	100	1K	10K	50K	250K	2Meg
20	200	2K	20K	100K	500K	
50	500	5K	25K	200K	1Meg	

Standard: Boxes

Capacity = 100 Units

Option: Tubes

All units oriented with #1 pin to same side.

	Pin Style		P, PM	X, XL, XW, RW
Magazine	Width	=	0.47"	0.29"
	Height	=	0.54"	0.76"
	Length	=	20.5"	20.1"
	Capacity	=	50 Units	50 Units

Option: Tape & Reel, Ammo Pack (Available only for 72RW only)

All units oriented with #1 pin to the right of the direction of feed.

	Seat Plane to Centerline of Sprocket Hole	=	.71" (18.03 mm)
Tape	Width	=	18 mm
	Sprocket	=	Single Hole .50" spacing
	Capacity	=	1,000 Units
Reel	Diameter	=	14" (356mm)
Ammo	Tape Fold	=	12" (305mm)
	Box	=	1.8" x 13" x 10" (46mm x 330mm x 254mm)

ORDERING INFORMATION

Standard:

Model Series ——— **72** **P** **R** **10K** ——— Resistance Value
 Pin Style ——— Resistance Prefix

Option:

Pin Style ——— **72** **W** **R** **10K** **TB** ——— Packaging Option:
 TB = Tubes
 (Pin styles P, PM, X, XL, XW, RW)

Option:

Pin Style ——— **72** **RW** **F** **R** **10K** **TR** ——— Packaging Option:
 AP = Ammo pack
 TR = Tape & Reel
 (Pin style RW only)


Pin Style Suffix: ———
 (Used with AP and TR packaging options.
 Applicable to pin style RW only.
 "F" designates 0.70" lead length.)

Option:

Pin Style ——— **72** **X** **T** **R** **10K** ———

Adjustment Options: ———
 T = Knob Option
 Applicable to pin style X & P only.
 E = Extended Rotor Option
 Applicable to all pin styles.

CIRCUIT DIAGRAM



NOTES

Metric equivalents, based on 1 inch = 25.4mm are rounded to the same number of significant figures as in the original English units and are provided for general information only.

Tolerances unless otherwise specified:
 Linear = $\pm .01$ inches (.25mm)
 Angular = ± 2 degrees

