

(2,54mm) .100"

SS, SD, ESD, ESS, HSS SERIES

PRECISION MACHINED SOCKET STRIPS

Mates with:
TS, TD, HTS, BBS,
BBD, BBL, BDL, BHS,

SPECIFICATIONS

For complete specifications see www.samtec.com?SS, www.samtec.com?ESS, www.samtec.com?SD or www.samtec.com?ESD

SS, SD, ESS, ESD

Insulator Material:
Black G.F. Polyester

Contact:
BeCu

Shell:
Brass

except Style 5A
Phosphor Bronze

Current Rating: 1A

Plating:

Au over 50μ" (1,27μm) Ni or
Sn over 50μ" (1,27μm) Ni

Operating Temp Range:
-55°C to +125°C

Contact Resistance:
10 mΩ max

Insertion Force:
(Single contact only)

Standard=

9oz (2,50N) avg.,

16oz (4,45N) max

Low Insertion Force=

2.5oz (0,70N) avg.,

5.5oz (1,53N) max

Withdrawal Force:
(Single contact only)

Standard=

2.5oz (0,70N) avg.,

1.5oz (0,42N) min

Low Insertion Force=

2.0oz (0,56N) avg.,

0.35oz (0,10N) min

Insertion Depth:

(-05 thru -08, -1X & -21X, -5A)

(3,18mm) .125" to

(3,99mm) .157"

Insertion Depth: (-2, -22, -38)

(2,41mm) .095" to

(3,68mm) .145"

Insertion Depth: (-7)

(2,41mm) .095" to

(3,51mm) .138"

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

SPECIFICATIONS

For complete specifications see www.samtec.com?HSS

HSS

Same as SS except:

Insulator Material:

Black Liquid Crystal Polymer

Max Processing Temp:

230°C for 60 seconds, or

260°C for 20 seconds 3x with

all Au

Lead-Free Solderable:

Wave, or reflow with all Au

TYPE STRIP

1

NO. PINS PER ROW

PLATING OPTION

LEAD STYLE

OPTION

OTHER OPTION

01 thru 32

= SS, ESS Series

01 thru 36

= HSS, SD & ESD Series

SS

= Standard Single Row Socket


HSS

= High Temp Single Row Socket

ESS

= Elevated Single Row Socket

Styles -5A & -05 thru -08 socket heads not countersunk.




SD

= Standard Double Row Socket

ESD

= Elevated Double Row Socket

Style -5A not available.
Styles -5A & -05 thru -08 socket heads not countersunk.



LIF= Low Insertion Force

Note:
Some lengths, styles and options are non-standard, non-returnable.

-S

= 10μ" (0,25μm) Gold contact,
Tin shell
(Styles 2 & 22 only)

-T

= 30μ" (0,76μm) Gold contact,
Tin shell

-G


= 30μ" (0,76μm) Gold contact,
10μ" (0,25μm) Gold shell

-TT


= Tin contact and shell
(Styles 1, 2, 18 and 21 only)
(and 05 thru 08, except LIF N/A)

-L = Locking Socket

Add -L suffix for locking lead socket in end positions. Requires Style -2 or -22 and .035" ± .003 DIA board hole.



-N = Non Flush




ALSO AVAILABLE

Locking lead option on ESS and ESD series. Contact Samtec.

-1A, -1B or -1C


For LIF specify -21A, -21B or -21C
(SS, HSS, SD)



LEAD STYLE	Y
-1A or -21A	(9,14) .360
-1B or -21B	(12,95) .510
-1C or -21C	(6,60) .260

-2, -22*, -5A,
-7 or -38*

*For LIF specify -22 or -38 (SS, HSS, SD)




LEAD STYLE	X DIA	Y	Z
-2 or -22	(0,51) .020	(3,18) .125	(7,62) .300
-38	(0,51) .020	(4,57) .180	(8,89) .350
-7	(0,64) .025	(10,41) .410	(15,24) .600
-5A	(0,89) .035	(12,95) .510	(17,86) .703

Locking lead available. See OPTION.

-05, -06, -08

For LIF specify
-25, -26, -28
(ESS, ESD)



LEAD STYLE	A	B	C
05 or 25	(17,86) .703	(13,46) .530	(4,39) .173
06 or 26	(14,05) .553	(8,38) .330	(5,66) .223
08 or 28	(17,86) .703	(8,38) .330	(9,47) .373

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329 SAMTEC UK • Tel: 44 01236 739292
SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112 SAMTEC ANZ • Tel: 613 9512 7747