


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		AA	REV PER ECO-14-004910	01APR14	GG	JG

D

C

B

A



- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: HOUSING—POLYCARBONATE,CLEAR.
TERMINAL – .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178μm[.000007] THICK GOLD IN LOCALIZED PLATE AREA, OVER .762μm[.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54μm[.000100] THICK NICKEL ON ENTIRE CONTACT.
3.

PLUG WILL ACCEPT 26 OR 28 AWG STRANDED WIRE HAVING A MAXIMUM INSULATION DIAMETER OF 0.99[.039] AND A MAXIMUM DIAMETER ROUND CABLE JACKET OF 2.54 [.100] OR OVAL CABLE JACKET OF 2.29 × 4.83[.090 × .190] MAXIMUM.
- 4

TERMINATED DIMENSION 6.15[.242] MAXIMUM.
- 5

10 ASSEMBLIES PER PACKAGE.
- 6

10,000 ASSEMBLES PER PACKAGE.
- 7

1000 ASSEMBLIES PER PACKAGE.
- 8

100 ASSEMBLIES PER PACKAGE.
- 10

REELED PRODUCT ON STRIP DOES NOT HAVE VOID CORING ILLUSTRATED ON THIS DRAWING.

D

C

641335

B

A

SUPERSEDED BY 5-641335-7	5	6-641335-3
	8	5-641335-3
	7	5-641335-2
	6	5-641335-1
OBSOLETE	REELED 10	641335-1
	PACKAGED	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN YTP/UTA 9-1-93		TE TE Connectivity							
DIMENSIONS: mm [INCHES]			CHK C.WHITT 9-15-93									
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MODULAR PLUG ASSEMBLY, 4 POSITION, LINE —							
			0 PLC ± — 1									
			1 PLC ± —									
			2 PLC ± —									
			APVD J.TONEY 9-20-93		SIZE A2							
			PRODUCT SPEC 108-1163						CAGE CODE 00779			
			APPLICATION SPEC 114-6016									
MATERIAL — 2			WEIGHT —		RESTRICTED TO —							
FINISH — 2			CUSTOMER DRAWING						SCALE 4:1			
					SHEET 1 of 1							
					REV AA							