

# 74ACQ573, 74ACTQ573 Quiet Series™ Octal Latch with 3-STATE Outputs

## Features

- $I_{CC}$  and  $I_{OZ}$  reduced by 50%
- Guaranteed simultaneous switching noise level and dynamic threshold performance
- Guaranteed pin-to-pin skew AC performance
- Improved latch-up immunity
- Inputs and outputs on opposite sides of package allow easy interface with microprocessors
- Outputs source/sink 24mA

## General Description


The ACQ/ACTQ573 is a high-speed octal latch with buffered common Latch Enable (LE) and buffered common Output Enable ( $\overline{OE}$ ) inputs. The ACQ/ACTQ573 is functionally identical to the ACQ/ACTQ373 but with inputs and outputs on opposite sides of the package. The ACQ/ACTQ utilizes Fairchild's Quiet Series™ technology to guarantee quiet output switching and improved dynamic threshold performance. FACT Quiet Series™ features GTO™ output control and undershoot corrector in addition to a split ground bus for superior performance.

## Ordering Information

| Order Number | Package Number | Package Description                                                         |
|--------------|----------------|-----------------------------------------------------------------------------|
| 74ACQ573SC   | M20B           | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  |
| 74ACQ573SJ   | M20D           | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide               |
| 74ACQ573MTC  | MTC20          | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| 74ACTQ573SC  | M20B           | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  |
| 74ACTQ573SJ  | M20D           | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide               |
| 74ACTQ573QSC | MQA20          | 20-Lead Quarter Size Outline Package (QSOP), JEDEC MO-137, 0.150" Wide      |
| 74ACTQ573MTC | MTC20          | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |

Device also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering number.

## Connection Diagram




## Pin Descriptions


| Pin Names       | Description                 |
|-----------------|-----------------------------|
| $D_0$ – $D_7$   | Data Inputs                 |
| LE              | Latch Enable Input          |
| $\overline{OE}$ | 3-STATE Output Enable Input |
| $O_0$ – $O_7$   | 3-STATE Latch Outputs       |

FACT™, Quiet Series™, FACT Quiet Series™, and GTO™ are trademarks of Fairchild Semiconductor Corporation.

## Logic Symbol



IEEE/IEC



## Functional Description

The ACQ/ACTQ573 contains eight D-type latches with 3-STATE output buffers. When the Latch Enable (LE) input is HIGH, data on the  $D_n$  inputs enters the latches. In this condition the latches are transparent, i.e., a latch output will change state each time its D-type input changes. When LE is LOW the latches store the information that was present on the D-type inputs at setup time preceding the HIGH-to-LOW transition of LE. The 3-STATE buffers are controlled by the Output Enable ( $\overline{OE}$ ) input. When  $\overline{OE}$  is LOW, the buffers are enabled. When  $\overline{OE}$  is HIGH the buffers are in the high impedance mode but this does not interfere with entering new data into the latches.

## Truth Table

| Inputs          |    |   | Outputs |
|-----------------|----|---|---------|
| $\overline{OE}$ | LE | D | $O_n$   |
| L               | H  | H | H       |
| L               | H  | L | L       |
| L               | L  | X | $O_0$   |
| H               | X  | X | Z       |

H = HIGH Voltage


L = LOW Voltage

Z = High Impedance

X = Immaterial

$O_0$  = Previous  $O_0$  before HIGH-to-LOW transition of Latch Enable

## Logic Diagram



Please note that this diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays.

## Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

| Symbol                | Parameter                                                         | Rating                   |
|-----------------------|-------------------------------------------------------------------|--------------------------|
| $V_{CC}$              | Supply Voltage                                                    | −0.5V to +7.0V           |
| $I_{IK}$              | DC Input Diode Current<br>$V_I = -0.5V$<br>$V_I = V_{CC} + 0.5V$  | −20mA<br>+20mA           |
| $V_I$                 | DC Input Voltage                                                  | −0.5V to $V_{CC} + 0.5V$ |
| $I_{OK}$              | DC Output Diode Current<br>$V_O = -0.5V$<br>$V_O = V_{CC} + 0.5V$ | −20mA<br>+20mA           |
| $V_O$                 | DC Output Voltage                                                 | −0.5V to $V_{CC} + 0.5V$ |
| $I_O$                 | DC Output Source or Sink Current                                  | ±50mA                    |
| $I_{CC}$ or $I_{GND}$ | DC $V_{CC}$ or Ground Current per Output Pin                      | ±50mA                    |
| $T_{STG}$             | Storage Temperature                                               | −65°C to +150°C          |
|                       | DC Latch-Up Source or Sink Current                                | ±300mA                   |
| $T_J$                 | Junction Temperature                                              | 140°C                    |

## Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

| Symbol                | Parameter                                                                                                   | Rating                       |
|-----------------------|-------------------------------------------------------------------------------------------------------------|------------------------------|
| $V_{CC}$              | Supply Voltage<br>ACQ<br>ACTQ                                                                               | 2.0V to 6.0V<br>4.5V to 5.5V |
| $V_I$                 | Input Voltage                                                                                               | 0V to $V_{CC}$               |
| $V_O$                 | Output Voltage                                                                                              | 0V to $V_{CC}$               |
| $T_A$                 | Operating Temperature                                                                                       | −40°C to +85°C               |
| $\Delta V / \Delta t$ | Minimum Input Edge Rate, ACQ Devices:<br>$V_{IN}$ from 30% to 70% of $V_{CC}$ , $V_{CC}$ @ 3.0V, 4.5V, 5.5V | 125mV/ns                     |
| $\Delta V / \Delta t$ | Minimum Input Edge Rate, ACTQ Devices:<br>$V_{IN}$ from 0.8V to 2.0V, $V_{CC}$ @ 4.5V, 5.5V                 | 125mV/ns                     |

## DC Electrical Characteristics for ACQ

| Symbol                         | Parameter                                     | V <sub>CC</sub> (V) | Conditions                                                                                                                                     | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> = –40°C to +85°C |  | Units |
|--------------------------------|-----------------------------------------------|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|-------------------|---------------------------------|--|-------|
|                                |                                               |                     |                                                                                                                                                | Typ.                   | Guaranteed Limits |                                 |  |       |
| V <sub>IH</sub>                | Minimum HIGH Level Input Voltage              | 3.0                 | V <sub>OUT</sub> = 0.1V or V <sub>CC</sub> – 0.1V                                                                                              | 1.5                    | 2.1               | 2.1                             |  | V     |
|                                |                                               | 4.5                 |                                                                                                                                                | 2.25                   | 3.15              | 3.15                            |  |       |
|                                |                                               | 5.5                 |                                                                                                                                                | 2.75                   | 3.85              | 3.85                            |  |       |
| V <sub>IL</sub>                | Maximum LOW Level Input Voltage               | 3.0                 | V <sub>OUT</sub> = 0.1V or V <sub>CC</sub> – 0.1V                                                                                              | 1.5                    | 0.9               | 0.9                             |  | V     |
|                                |                                               | 4.5                 |                                                                                                                                                | 2.25                   | 1.35              | 1.35                            |  |       |
|                                |                                               | 5.5                 |                                                                                                                                                | 2.75                   | 1.65              | 1.65                            |  |       |
| V <sub>OH</sub>                | Minimum HIGH Level Output Voltage             | 3.0                 | I <sub>OUT</sub> = –50μA                                                                                                                       | 2.99                   | 2.9               | 2.9                             |  | V     |
|                                |                                               | 4.5                 |                                                                                                                                                | 4.49                   | 4.4               | 4.4                             |  |       |
|                                |                                               | 5.5                 |                                                                                                                                                | 5.49                   | 5.4               | 5.4                             |  |       |
|                                |                                               | 3.0                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ;<br>I <sub>OH</sub> = –12mA                                                              |                        | 2.56              | 2.46                            |  |       |
|                                |                                               | 4.5                 | I <sub>OH</sub> = –24mA                                                                                                                        |                        | 3.86              | 3.76                            |  |       |
|                                |                                               | 5.5                 | I <sub>OH</sub> = –24mA <sup>(1)</sup>                                                                                                         |                        | 4.86              | 4.76                            |  |       |
| V <sub>OL</sub>                | Maximum LOW Level Output Voltage              | 3.0                 |                                                                                                                                                | 0.002                  | 0.1               | 0.1                             |  | V     |
|                                |                                               | 4.5                 | I <sub>OUT</sub> = 50μA                                                                                                                        | 0.001                  | 0.1               | 0.1                             |  |       |
|                                |                                               | 5.5                 |                                                                                                                                                | 0.001                  | 0.1               | 0.1                             |  |       |
|                                |                                               | 3.0                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ;<br>I <sub>OL</sub> = 12mA                                                               |                        | 0.36              | 0.44                            |  |       |
|                                |                                               | 4.5                 | I <sub>OL</sub> = 24mA                                                                                                                         |                        | 0.36              | 0.44                            |  |       |
|                                |                                               | 5.5                 | I <sub>OL</sub> = 24mA <sup>(1)</sup>                                                                                                          |                        | 0.36              | 0.44                            |  |       |
| I <sub>IN</sub> <sup>(3)</sup> | Maximum Input Leakage Current                 | 5.5                 | V <sub>I</sub> = V <sub>CC</sub> , GND                                                                                                         |                        | ± 0.1             | ± 1.0                           |  | μA    |
| I <sub>OLD</sub>               | Minimum Dynamic Output Current <sup>(2)</sup> | 5.5                 | V <sub>OLD</sub> = 1.65 V <sub>Max</sub>                                                                                                       |                        |                   | 75                              |  | mA    |
| I <sub>OHD</sub>               |                                               | 5.5                 | V <sub>OHD</sub> = 3.85 V <sub>Min</sub>                                                                                                       |                        |                   | –75                             |  | mA    |
| I <sub>CC</sub> <sup>(3)</sup> | Maximum Quiescent Supply Current              | 5.5                 | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                                       |                        | 4.0               | 40.0                            |  | μA    |
| I <sub>OZ</sub>                | Maximum 3-STATE Leakage Current               | 5.5                 | V <sub>I</sub> (OE) = V <sub>IL</sub> , V <sub>IH</sub> ;<br>V <sub>I</sub> = V <sub>CC</sub> , GND;<br>V <sub>O</sub> = V <sub>CC</sub> , GND |                        | ±0.25             | ±2.5                            |  | μA    |
| V <sub>OLP</sub>               | Quiet Output Maximum Dynamic V <sub>OL</sub>  | 5.0                 | Figures 1 & 2 <sup>(4)</sup>                                                                                                                   | 1.1                    | 1.5               |                                 |  | V     |
| V <sub>OLV</sub>               | Quiet Output Minimum Dynamic V <sub>OL</sub>  | 5.0                 | Figures 1 & 2 <sup>(4)</sup>                                                                                                                   | –0.6                   | –1.2              |                                 |  | V     |
| V <sub>IHD</sub>               | Minimum HIGH Level Dynamic Input Voltage      | 5.0                 | <sup>(5)</sup>                                                                                                                                 | 3.1                    | 3.5               |                                 |  | V     |
| V <sub>ILD</sub>               | Maximum LOW Level Dynamic Input Voltage       | 5.0                 | <sup>(5)</sup>                                                                                                                                 | 1.9                    | 1.5               |                                 |  | V     |

**Notes:**

1. All outputs loaded; thresholds on input associated with output under test.
2. Maximum test duration 2.0ms, one output loaded at a time.
3. I<sub>IN</sub> and I<sub>CC</sub> @ 3.0V are guaranteed to be less than or equal to the respective limit @ 5.5V V<sub>CC</sub>.
4. Max number of outputs defined as (n). Data Inputs are driven 0V to 5V. One output @ GND.
5. Max number of Data Inputs (n) switching. (n – 1) Inputs switching 0V to 5V (ACQ). Input-under-test switching: 5V to threshold (V<sub>ILD</sub>), 0V to threshold (V<sub>IHD</sub>), f = 1MHz.

## DC Electrical Characteristics for ACTQ

| Symbol           | Parameter                                     | V <sub>CC</sub> (V) | Conditions                                                                                     | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> = −40°C to +85°C |  | Units |
|------------------|-----------------------------------------------|---------------------|------------------------------------------------------------------------------------------------|------------------------|-------------------|---------------------------------|--|-------|
|                  |                                               |                     |                                                                                                | Typ.                   | Guaranteed Limits |                                 |  |       |
| V <sub>IH</sub>  | Minimum HIGH Level Input Voltage              | 4.5                 | V <sub>OUT</sub> = 0.1V or V <sub>CC</sub> − 0.1V                                              | 1.5                    | 2.0               | 2.0                             |  | V     |
|                  |                                               | 5.5                 |                                                                                                | 1.5                    | 2.0               | 2.0                             |  |       |
| V <sub>IL</sub>  | Maximum LOW Level Input Voltage               | 4.5                 | V <sub>OUT</sub> = 0.1V or V <sub>CC</sub> − 0.1V                                              | 1.5                    | 0.8               | 0.8                             |  | V     |
|                  |                                               | 5.5                 |                                                                                                | 1.5                    | 0.8               | 0.8                             |  |       |
| V <sub>OH</sub>  | Minimum HIGH Level Output Voltage             | 4.5                 | I <sub>OUT</sub> = −50μA                                                                       | 4.49                   | 4.4               | 4.4                             |  | V     |
|                  |                                               | 5.5                 |                                                                                                | 5.49                   | 5.4               | 5.4                             |  |       |
|                  |                                               | 4.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ;<br>I <sub>OH</sub> = −24mA              |                        | 3.86              | 3.76                            |  |       |
|                  |                                               | 5.5                 | I <sub>OH</sub> = −24mA <sup>(6)</sup>                                                         |                        | 4.86              | 4.76                            |  |       |
| V <sub>OL</sub>  | Maximum LOW Level Output Voltage              | 4.5                 | I <sub>OUT</sub> = 50μA                                                                        | 0.001                  | 0.1               | 0.1                             |  | V     |
|                  |                                               | 5.5                 |                                                                                                | 0.001                  | 0.1               | 0.1                             |  |       |
|                  |                                               | 4.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ;<br>I <sub>OL</sub> = 24mA               |                        | 0.36              | 0.44                            |  |       |
|                  |                                               | 5.5                 | I <sub>OL</sub> = 24mA <sup>(6)</sup>                                                          |                        | 0.36              | 0.44                            |  |       |
| I <sub>IN</sub>  | Maximum Input Leakage Current                 | 5.5                 | V <sub>I</sub> = V <sub>CC</sub> , GND                                                         |                        | ±0.1              | ±1.0                            |  | μA    |
| I <sub>OZ</sub>  | Maximum 3-STATE Leakage Current               | 5.5                 | V <sub>I</sub> = V <sub>IL</sub> , V <sub>IH</sub> ;<br>V <sub>O</sub> = V <sub>CC</sub> , GND |                        | ±0.25             | ±2.5                            |  | μA    |
| I <sub>CCT</sub> | Maximum I <sub>CC</sub> /Input                | 5.5                 | V <sub>I</sub> = V <sub>CC</sub> − 2.1V                                                        | 0.6                    |                   | 1.5                             |  | mA    |
| I <sub>OLD</sub> | Minimum Dynamic Output Current <sup>(7)</sup> | 5.5                 | V <sub>OLD</sub> = 1.65V Max.                                                                  |                        |                   | 75                              |  | mA    |
| I <sub>OHD</sub> |                                               | 5.5                 | V <sub>OHD</sub> = 3.85V Min.                                                                  |                        |                   | −75                             |  | mA    |
| I <sub>CC</sub>  | Maximum Quiescent Supply Current              | 5.5                 | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                       |                        | 4.0               | 40.0                            |  | μA    |
| V <sub>OLP</sub> | Quiet Output Maximum Dynamic V <sub>OL</sub>  | 5.0                 | Figures 1 & 2 <sup>(8)</sup>                                                                   | 1.1                    | 1.5               |                                 |  | V     |
| V <sub>OLV</sub> | Quiet Output Minimum Dynamic V <sub>OL</sub>  | 5.0                 | Figures 1 & 2 <sup>(8)</sup>                                                                   | −0.6                   | −1.2              |                                 |  | V     |
| V <sub>IHD</sub> | Minimum HIGH Level Dynamic Input Voltage      | 5.0                 | <sup>(9)</sup>                                                                                 | 1.9                    | 2.2               |                                 |  | V     |
| V <sub>ILD</sub> | Maximum LOW Level Dynamic Input Voltage       | 5.0                 | <sup>(9)</sup>                                                                                 | 1.2                    | 0.8               |                                 |  | V     |

## Notes:

- All outputs loaded; thresholds on input associated with output under test.
- Maximum test duration 2.0ms, one output loaded at a time.
- Max number of outputs defined as (n). Data Inputs are driven 0V to 3V. One output @ GND.
- Max number of data inputs (n) switching. (n - 1) inputs switching 0V to 3V (ACTQ). Input-under-test switching: 3V to threshold (V<sub>ILD</sub>), 0V to threshold (V<sub>IHD</sub>), f = 1MHz.

**AC Electrical Characteristics for ACQ**

| Symbol                  | Parameter                                                | $V_{CC}$ (V) <sup>(10)</sup> | $T_A = +25^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      |      | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      | Units |
|-------------------------|----------------------------------------------------------|------------------------------|----------------------------------------------------|------|------|--------------------------------------------------------------------------|------|-------|
|                         |                                                          |                              | Min.                                               | Typ. | Max. | Min.                                                                     | Max. |       |
| $t_{PHL}$ , $t_{PLH}$   | Propagation Delay,<br>$D_n$ to $O_n$                     | 3.3                          | 2.5                                                | 8.5  | 10.5 | 2.5                                                                      | 11.0 | ns    |
|                         |                                                          | 5.0                          | 1.5                                                | 5.5  | 7.0  | 1.5                                                                      | 7.5  |       |
| $t_{PLH}$ , $t_{PHL}$   | Propagation Delay,<br>LE to $O_n$                        | 3.3                          | 2.5                                                | 8.5  | 12.0 | 2.5                                                                      | 12.5 | ns    |
|                         |                                                          | 5.0                          | 2.0                                                | 6.0  | 8.0  | 2.0                                                                      | 8.5  |       |
| $t_{PZL}$ , $t_{PZH}$   | Output Enable Time                                       | 3.3                          | 2.5                                                | 8.5  | 13.0 | 2.5                                                                      | 13.5 | ns    |
|                         |                                                          | 5.0                          | 1.5                                                | 6.0  | 8.5  | 1.5                                                                      | 9.0  |       |
| $t_{PHZ}$ , $t_{PLZ}$   | Output Disable Time                                      | 3.3                          | 1.0                                                | 9.0  | 14.5 | 1.0                                                                      | 15.0 | ns    |
|                         |                                                          | 5.0                          | 1.0                                                | 6.0  | 9.5  | 1.0                                                                      | 10.0 |       |
| $t_{OSHL}$ , $t_{OSLH}$ | Output to Output Skew,<br>$D_n$ to $O_n$ <sup>(11)</sup> | 3.3                          |                                                    | 1.0  | 1.5  |                                                                          | 1.5  | ns    |
|                         |                                                          | 5.0                          |                                                    | 0.5  | 1.0  |                                                                          | 1.0  |       |

**Notes:**

10. Voltage range 5.0 is  $5.0\text{V} \pm 0.5\text{V}$ . Voltage range 3.3 is  $3.3\text{V} \pm 0.3\text{V}$ .

11. Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW ( $t_{OSHL}$ ) or LOW-to-HIGH ( $t_{OSLH}$ ). Parameter guaranteed by design.

**AC Operating Requirements for ACQ**

| Symbol         | Parameter                                        | V <sub>CC</sub> (V) <sup>(12)</sup> | T <sub>A</sub> = +25°C,<br>C <sub>L</sub> = 50pF |                    | T <sub>A</sub> = −40°C to +85°C,<br>C <sub>L</sub> = 50pF | Units |
|----------------|--------------------------------------------------|-------------------------------------|--------------------------------------------------|--------------------|-----------------------------------------------------------|-------|
|                |                                                  |                                     | Typ.                                             | Guaranteed Minimum |                                                           |       |
| t <sub>S</sub> | Setup Time, HIGH or LOW,<br>D <sub>n</sub> to LE | 3.3                                 | 0                                                | 3.0                | 3.0                                                       | ns    |
|                |                                                  | 5.0                                 | 0                                                | 3.0                | 3.0                                                       |       |
| t <sub>H</sub> | Hold Time, HIGH or LOW,<br>D <sub>n</sub> to LE  | 3.3                                 | 0                                                | 1.5                | 1.5                                                       | ns    |
|                |                                                  | 5.0                                 | 0                                                | 1.5                | 1.5                                                       |       |
| t <sub>W</sub> | LE Pulse Width, HIGH                             | 3.3                                 | 2.0                                              | 4.0                | 4.0                                                       | ns    |
|                |                                                  | 5.0                                 | 2.0                                              | 4.0                | 4.0                                                       |       |

**Note:**

12. Voltage range 5.0 is  $5.0\text{V} \pm 0.5\text{V}$ . Voltage range 3.3 is  $3.3\text{V} \pm 0.3\text{V}$ .

**AC Electrical Characteristics for ACTQ**

| Symbol               | Parameter                                                | $V_{CC}$ (V) <sup>(13)</sup> | $T_A = +25^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      |      | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      | Units |
|----------------------|----------------------------------------------------------|------------------------------|----------------------------------------------------|------|------|--------------------------------------------------------------------------|------|-------|
|                      |                                                          |                              | Min.                                               | Typ. | Max. | Min.                                                                     | Max. |       |
| $t_{PHL}, t_{PLH}$   | Propagation Delay,<br>$D_n$ to $O_n$                     | 5.0                          | 2.0                                                | 6.5  | 7.5  | 2.0                                                                      | 8.0  | ns    |
| $t_{PLH}, t_{PHL}$   | Propagation Delay,<br>LE to $O_n$                        | 5.0                          | 2.5                                                | 7.0  | 8.5  | 2.5                                                                      | 9.0  | ns    |
| $t_{PZL}, t_{PZH}$   | Output Enable Time                                       | 5.0                          | 2.0                                                | 7.0  | 9.0  | 2.0                                                                      | 9.5  | ns    |
| $t_{PHZ}, t_{PLZ}$   | Output Disable Time                                      | 5.0                          | 1.0                                                | 8.0  | 10.0 | 1.0                                                                      | 10.5 | ns    |
| $t_{OSHL}, t_{OSLH}$ | Output to Output Skew,<br>$D_n$ to $O_n$ <sup>(14)</sup> | 5.0                          |                                                    | 0.5  | 1.0  |                                                                          | 1.0  | ns    |

**Note:**

13. Voltage range 5.0 is  $5.0\text{V} \pm 0.5\text{V}$ .

14. Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW ( $t_{OSHL}$ ) or LOW-to-HIGH ( $t_{OSLH}$ ). Parameter guaranteed by design.

**AC Operating Requirements for ACTQ**

| Symbol         | Parameter                                        | V <sub>CC</sub> (V) <sup>(15)</sup> | T <sub>A</sub> = +25°C,<br>C <sub>L</sub> = 50pF |                    | T <sub>A</sub> = −40°C to +85°C,<br>C <sub>L</sub> = 50pF | Units |
|----------------|--------------------------------------------------|-------------------------------------|--------------------------------------------------|--------------------|-----------------------------------------------------------|-------|
|                |                                                  |                                     | Typ.                                             | Guaranteed Minimum |                                                           |       |
| t <sub>S</sub> | Setup Time, HIGH or LOW,<br>D <sub>n</sub> to LE | 5.0                                 | 0                                                | 3.0                | 3.0                                                       | ns    |
| t <sub>H</sub> | Hold Time, HIGH or LOW,<br>D <sub>n</sub> to LE  | 5.0                                 | 0                                                | 1.5                | 1.5                                                       | ns    |
| t <sub>W</sub> | LE Pulse Width, HIGH                             | 5.0                                 | 2.0                                              | 4.0                | 4.0                                                       | ns    |

**Notes:**

15. Voltage range 5.0 is  $5.0\text{V} \pm 0.5\text{V}$ .

**Capacitance**

| Symbol   | Parameter                     | Conditions             | Typ. | Units |
|----------|-------------------------------|------------------------|------|-------|
| $C_{IN}$ | Input Capacitance             | $V_{CC} = \text{OPEN}$ | 4.5  | pF    |
| $C_{PD}$ | Power Dissipation Capacitance | $V_{CC} = 5.0\text{V}$ | 42.0 | pF    |

## FACT Noise Characteristics

The setup of a noise characteristics measurement is critical to the accuracy and repeatability of the tests. The following is a brief description of the setup used to measure the noise characteristics of FACT.

### Equipment:


Hewlett Packard Model 8180A Word Generator

PC-163A Test Fixture

Tektronics Model 7854 Oscilloscope

### Procedure:

1. Verify Test Fixture Loading: Standard Load 50pF, 500Ω.
2. Deskew the HFS generator so that no two channels have greater than 150ps skew between them. This requires that the oscilloscope be deskewed first. It is important to deskew the HFS generator channels before testing. This will ensure that the outputs switch simultaneously.
3. Terminate all inputs and outputs to ensure proper loading of the outputs and that the input levels are the correct voltage.
4. Set the HFS generator to toggle all but one output at a frequency of 1MHz. Greater frequencies will increase DUT heating and affect the results of the measurement.
5. Set the HFS generator input levels at 0V LOW and 3V HIGH for ACT devices and 0V LOW and 5V HIGH for AC devices. Verify levels with an oscilloscope.



### Notes:

16.  $V_{OHV}$  and  $V_{OLP}$  are measured with respect to ground reference.
17. Input pulses have the following characteristics:  
 $f = 1\text{MHz}$ ,  $t_r = 3\text{ns}$ ,  $t_f = 3\text{ns}$ , skew < 150ps.

Figure 1. Quiet Output Noise Voltage Waveforms

### $V_{OLP}/V_{OLV}$ and $V_{OHP}/V_{OHV}$ :

- Determine the quiet output pin that demonstrates the greatest noise levels. The worst case pin will usually be the furthest from the ground pin. Monitor the output voltages using a 50Ω coaxial cable plugged into a standard SMB type connector on the test fixture. Do not use an active FET probe.
- Measure  $V_{OLP}$  and  $V_{OLV}$  on the quiet output during the worst case transition for active and enable.
- Measure  $V_{OHP}$  and  $V_{OHV}$  on the quiet output during the worst case active and enable transition.
- Verify that the GND reference recorded on the oscilloscope has not drifted to ensure the accuracy and repeatability of the measurements.

### $V_{ILD}$ and $V_{IHD}$ :

- Monitor one of the switching outputs using a 50Ω coaxial cable plugged into a standard SMB type connector on the test fixture. Do not use an active FET probe.
- First increase the input LOW voltage level,  $V_{IL}$ , until the output begins to oscillate or steps out a min of 2ns. Oscillation is defined as noise on the output LOW level that exceeds  $V_{IL}$  limits, or on output HIGH levels that exceed  $V_{IH}$  limits. The input LOW voltage level at which oscillation occurs is defined as  $V_{ILD}$ .
- Next decrease the input HIGH voltage level,  $V_{IH}$ , until the output begins to oscillate or steps out a min of 2ns. Oscillation is defined as noise on the output LOW level that exceeds  $V_{IL}$  limits, or on output HIGH levels that exceed  $V_{IH}$  limits. The input HIGH voltage level at which oscillation occurs is defined as  $V_{IHD}$ .
- Verify that the GND reference recorded on the oscilloscope has not drifted to ensure the accuracy and repeatability of the measurements.





Figure 2. Simultaneous Switching Test Circuit



## Physical Dimensions


Dimensions are in inches (millimeters) unless otherwise noted.



**Figure 3. 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  
Package Number M20B**

# Physical Dimensions (Continued)

Dimensions are in millimeters unless otherwise noted.




M20DREVC

**Figure 4. 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide  
Package Number M20D**

# Physical Dimensions (Continued)

Dimensions are in millimeters unless otherwise noted.



## NOTES :



- THIS PACKAGE CONFORMS TO JEDEC MO-137 VARIATION AD
- PRIMARY DIMENSIONS IN MILLIMETERS  
REFERENCE DIMENSIONS IN INCHES
- DRAWING CONFORMS TO ASME Y14.5M-1994
- DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.

MQA20REVA



**Figure 5. 20-Lead Quarter Size Outline Package (QSOP), JEDEC MO-137, 0.150" Wide  
Package Number MQA20**

### Physical Dimensions (Continued)

Dimensions are in millimeters unless otherwise noted.



DIMENSIONS ARE IN MILLIMETERS



DETAIL A

NOTES:

- A. CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION AC,  
REF NOTE 6, DATE 7/93.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLDS FLASH,  
AND TIE BAR EXTRUSIONS.
- D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

MTC20REVD1

**Figure 6. 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide  
Package Number MTC20**



## TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

|                                                  |                                |                                                                                     |                             |
|--------------------------------------------------|--------------------------------|-------------------------------------------------------------------------------------|-----------------------------|
| ACE <sup>®</sup>                                 | HiSeC <sup>™</sup>             | Programmable Active Droop <sup>™</sup>                                              | TinyLogic <sup>®</sup>      |
| Across the board. Around the world. <sup>™</sup> | <i>i-Lo</i> <sup>™</sup>       | QFET <sup>®</sup>                                                                   | TINYOPTO <sup>™</sup>       |
| ActiveArray <sup>™</sup>                         | ImpliedDisconnect <sup>™</sup> | QS <sup>™</sup>                                                                     | TinyPower <sup>™</sup>      |
| Bottomless <sup>™</sup>                          | IntelliMAX <sup>™</sup>        | QT Optoelectronics <sup>™</sup>                                                     | TinyWire <sup>™</sup>       |
| Build it Now <sup>™</sup>                        | ISOPLANAR <sup>™</sup>         | Quiet Series <sup>™</sup>                                                           | TruTranslation <sup>™</sup> |
| CoolFET <sup>™</sup>                             | MICROCOUPLER <sup>™</sup>      | RapidConfigure <sup>™</sup>                                                         | μSerDes <sup>™</sup>        |
| CROSSVOLT <sup>™</sup>                           | MicroPak <sup>™</sup>          | RapidConnect <sup>™</sup>                                                           | UHC <sup>®</sup>            |
| CTL <sup>™</sup>                                 | MICROWIRE <sup>™</sup>         | ScalarPump <sup>™</sup>                                                             | UniFET <sup>™</sup>         |
| Current Transfer Logic <sup>™</sup>              | MSX <sup>™</sup>               | SMART START <sup>™</sup>                                                            | VCX <sup>™</sup>            |
| DOVE <sup>™</sup>                                | MSXPro <sup>™</sup>            | SPM <sup>®</sup>                                                                    | Wire <sup>™</sup>           |
| E <sup>2</sup> CMOS <sup>™</sup>                 | OCX <sup>™</sup>               | STEALTH <sup>™</sup>                                                                |                             |
| EcoSPARK <sup>®</sup>                            | OCXPro <sup>™</sup>            | SuperFET <sup>™</sup>                                                               |                             |
| EnSigna <sup>™</sup>                             | OPTOLOGIC <sup>®</sup>         | SuperSOT <sup>™</sup> -3                                                            |                             |
| FACT Quiet Series <sup>™</sup>                   | OPTOPLANAR <sup>®</sup>        | SuperSOT <sup>™</sup> -6                                                            |                             |
| FACT <sup>®</sup>                                | PACMAN <sup>™</sup>            | SuperSOT <sup>™</sup> -8                                                            |                             |
| FAST <sup>®</sup>                                | POP <sup>™</sup>               | SyncFET <sup>™</sup>                                                                |                             |
| FASTr <sup>™</sup>                               | Power220 <sup>®</sup>          | TCM <sup>™</sup>                                                                    |                             |
| FPS <sup>™</sup>                                 | Power247 <sup>®</sup>          | The Power Franchise <sup>®</sup>                                                    |                             |
| FRFET <sup>®</sup>                               | PowerEdge <sup>™</sup>         |  ™ |                             |
| GlobalOptoisolator <sup>™</sup>                  | PowerSaver <sup>™</sup>        | TinyBoost <sup>™</sup>                                                              |                             |
| GTO <sup>™</sup>                                 | PowerTrench <sup>®</sup>       | TinyBuck <sup>™</sup>                                                               |                             |

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status         | Definition                                                                                                                                                                                               |
|--------------------------|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative or In Design | This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production       | This datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production        | This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.                                                   |
| Obsolete                 | Not In Production      | This datasheet contains specifications on a product that has been discontinued by Fairchild Semiconductor. The datasheet is printed for reference information only.                                      |

Rev. 124

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fairchild Semiconductor:

[74ACTQ573MTCX](#) [74ACTQ573SC](#) [74ACTQ573SJ](#) [74ACTQ573QSC](#) [74ACTQ573PC](#) [74ACTQ573SCX](#)  
[74ACTQ573QSCX](#)