

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

Tooling Drawing NO.
USB A: TR00662

LOC
GP

DIST
00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISE PER ECO-05-006320	01AUG05	TW	JH

Pos.4

Pos.1

1

3

5

4

2

25±5

830⁺⁰₋₅₀

TYCO P/N
T/D YYWW
MADE IN CHINA

LABEL

(25)

(13)

(35)

NOTES:

1. TESTED FOR CONTINUITY, SHORTS AND OPENS, HI-POT 630V FOR 10MS.

2. CABLE ASSEMBLY MEETS USB 2.0 STANDARDS.

3. EXPOSED CABLE BRAID IS NOT PERMISSIBLE BEYOND OVERMOLD.

4. THE FINAL CABLE ASSEMBLY MAXIMUM LENGTH NOT TO EXCEED 1000MM PER USB SPECIFICATIONS.

5. MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC

PIN ASSIGNMENT :

USB A

2

3

1

4

Shell

Pair 1

White(D-)

Green(D+)

Red(Vbus)

Black(Gnd)

Drain Braid

NC

NC

NC

NC

NC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN
BOVEY LIU

CHK
-

APVD
F.D. McCORKEL

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

25/FEB/02

15/MAR/02

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

CABLE ASSEMBLY, USB A TYPE TO NC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1487599

RESTRICTED TO
-

SCALE
1:1

SHEET
1 OF 1

REV
C

AMP 1470-19 REV 31MAR2000