







FCIconnect.com

Copyright FCI

PRODUCT NO

SEE TABLE



mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406 ISO 1101		MOD JACK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM/INCH scale 1:1	title
C	V91920	BKB	8/24/99	angles	linear		NET JACK II RJ45 SPECIAL
D	V92060	LP	10/20/99				SINGLE PORT ASS'Y SNAP PEG
E	V00462	CEK	02/01/00	0'±2'			dwg no
F	V12718	LP	1/22/02	dr	R. GRAPE	1/5/98	sheet 1 of 3 size
G	M05-0074	ERE	4/23/05	enr	B. MARSHALL	1/5/98	74326
H	M05-0191	MHT	9/07/05	chr	G. HULL	1/5/98	A3
J	M06-0224	ERE	6/12/06	app	B. MARSHALL	1/5/98	type
sheet	revision	J	J	J			Product Customer Drawing
index	sheet	1	2	3			

form: A3

PDM: Rev:J

STATUS:Released



Printed: Aug 01, 2008

PRODUCT NO
74326-50YXXXN
74326-50YXXXNLF


NET JACK MAGNETICS
OPTION CODE -XXX
SEE GES-12-020

SHIELD OPTION "N"
NICKEL PLATING

SPRING OPTION Y	DESCRIPTION (SEE SHEET 4 FOR OPTIONAL VIEWS)
1	SPRING ON TOP,BOTTOM AND BOTH SIDES
2	NO SPRINGS
3	SPRINGS ON TOP AND BOTTOM
4	SPRINGS ON TOP,BOTTOM AND 1 PER SIDE (STAGGERED)
5	SAME AS OPTION 4 EXCEPT OPPOSITE STAGGER



RECOMMENDED PANEL OPENING



RECOMMENDED P.C.B. LAYOUT
AS VIEWED FROM TOP SIDE (COMPONENT SIDE)

NOTES :

1. RECOMMENDED PCB THICKNESS 1.57 [0.062].
2. HOUSING MATL: HIGH TEMP. THERMOPLASTIC, COLOR BLACK, UL94V-0.
3. CONTACT MATL: COPPER ALLOY
MATING AREA PLATING: 1.27uM/50u" MIN Au OVER Ni.
SOLDER AREA PLATING: 2.54uM/100u" MIN TIN OVER Ni.
4. SHIELDING MAT'L: COPPER ALLOY.
PLATING: 74326-50YXXX 80u"/2u MIN. TIN PLEATED
PLATING: 74326-50YXXXN 30u"/.76u MIN.NICKEL PLEATED
5. ALL DIMENSIONS IN MILLIMETERS AND INCHES.
6. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M 1994.
7. PART NUMBERS WITH "LF" AT THE END ARE LEAD FREE.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
9. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

mat'l. code	surface	tolerance	projection	product family
-	ISO 1302	ISO 406		MOD JACK
ltr	ecn	no	dr	date
J				
	angles	linear		
	0°±2'			
	dr	R. GRAPE	1/5/98	
	enr	B. MARSHALL	1/5/98	
	chr	G. HULL	1/5/98	
	app	B. MARSHALL	1/5/98	
sheet	revision			
index	sheet			


tolerances unless otherwise specified	MM/INCH	scale 1:1	title
.X±.3/.01			NET JACK II RJ45 SPECIAL
.XX±.13/.005			SINGLE PORT ASS'Y SNAP PEG
.XXX±.051/.0020			dwg no
			sheet 2 of 3 size
			74326 A3
			type Product Customer Drawing

PRODUCT NO


SEE TABLE

SPRING TAB CONFIGURATIONS


OPTION Y




OPTION 1




OPTION 2



OPTION 3



OPTION 4



OPTION 5

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406 ISO 1101		MOD JACK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
J					angles linear		NET JACK II RJ45 SPECIAL
					0°±2'		SINGLE PORT ASS'Y SNAP PEG
							dwg no
				dr	R. GRAPE	1/5/98	sheet 2 of 3 size
				enr	B. MARSHALL	1/5/98	74326
				chr	G. HULL	1/5/98	A3
				app	B. MARSHALL	1/5/98	type
sheet	revision						Product Customer Drawing
index	sheet						

form: A3