



EVERLIGHT ELECTRONICS CO., LTD.

MODEL NO: 96-22UYC/S530-A2

Device Number : DSE-962-014 REV. 1.0

High Performance with Reflector LEDs

ECN : Page: 1/4


Features :

- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Eia std package.
- IC compatible.

Applications :

- Automotive: backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Indicator and backlight for audio and video equipment.
- Indicator and backlight for battery driven equipment.
- Small indicator for outdoor applications.
- Indicator and backlight in office equipment.
- Flat backlight for LED, switches and symbol.
- General use.

Package Dimension :



Notes :

Tolerances Unless Dimension $\pm 0.1\text{mm}$

Angle $\pm 0.5^\circ$

Unit = mm

PART NO	CHIP		Lens Color
	Material	Emitted Color	
96-22UYC/S530-A2	AlGaInP	Super Yellow	Water Clear

Office: NO 25, Lane. 76, Chung Yang Rd., Sec. 3, Tucheng, Taipei 236, Taiwan, R.O.C.

TEL: 886-2-2267-2000, 2266-9936(22 Lines)

FAX: 886-2-2267-6189

<http://www.everlight.com>



EVERLIGHT ELECTRONICS CO.,LTD.

MODEL NO: 96-22UYC/S530-A2

Device Number : DSE-962-014 REV. 1.0

High Performance with Reflector LEDs

ECN : Page: 2/4

■ Absolute Maximum Ratings at Ta = 25℃

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	25	mA
Operating Temperature	Topr	-40~+85	℃
Storage Temperature	Tstg	-40~+90	℃
Soldering Temperature	Tsol	245(for 5second)	℃
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	120	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	160	mA

■ Electronic Optical Characteristics :

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous intensity	Iv	-----	4	-----	mcd	If=2mA
		27	68	-----	mcd	If=20mA
Viewing Angle	2 θ 1/2	-----	145	-----	deg	If=20mA
Peak Wavelength	λ p	-----	591	-----	nm	If=20mA
Dominant Wavelength	λ d	-----	589	-----	nm	If=20mA
Spectrum Radiation Bandwidth	△ λ	-----	15	-----	nm	If=20mA
Forward Voltage	Vf	-----	4.0	4.8	V	If=20mA
Reverse Current	Ir	-----	-----	10	μ A	Vr=5V



EVERLIGHT ELECTRONICS CO.,LTD.

MODEL NO: 96-22UYC/S530-A2

Device Number : DSE-962-014 REV. 1.0

High Performance with Reflector LEDs

ECN : Page: 3/4

■ Reliability test item and condition

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 Pcs	0/1
2	Temperature Cycle	H : +85°C 30min ∫ 5 min L : -55°C 30min	50 CYCLE	76 Pcs	0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	50 CYCLE	76 Pcs	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 Pcs	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 Pcs	0/1
6	DC Operating Life	If = 20 mA	1000 HRS	76 Pcs	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 Pcs	0/1



EVERLIGHT ELECTRONICS CO.,LTD.

MODEL NO: 96-22UYC/S530-A2

Device Number : DSE-962-014 REV. 1.0

High Performance with Reflector LEDs

ECN : Page: 4/4

Typical Electro-Optical Characteristic Curves

