





PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S93C6PA00
15	39.14	33.32	25.18	24.54	19.18	D15S93C6PA00
25	53.03	47.04	39.12	38.25	33.12	D25S93C6PA00
						0.76µ gold


LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S93C6PA00LF
15	39.14	33.32	25.18	24.54	19.18	D15S93C6PA00LF
25	53.03	47.04	39.12	38.25	33.12	D25S93C6PA00LF
						0.76µ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		 mm		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	PESSON	2005/06/22	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2			
Eng	PESSON	2005/06/22			0.XX	±0.1					
Chr	LEGARE	2005/06/22			0.XX' ±2°	0.XXX		±0.1	ECN LS06-0140		
Appr	LEGARE	2005/06/22	Product family				D-SUB	Spec ref -			
			title FEMALE CONNECTOR DELTA D straight press-fit				dwg no C01-8646-0870		Rev. C		
			catalog no				-	CUSTOMER		sheet 1 of 1	

rev	ecn no	dr	date
A	-	MPE	2005/06/22
B	LS06-0097	LGO	2006/07/28
C	LS06-0140	LGO	2006/09/16
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-