



SUGGESTED MATING TAB






- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
- 2 - NO BURRS PERMISSIBLE AT HOLE.
- 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.
- 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



ASSEMBLY VIEW

1 PRELIMINARY - NOT FOR PRODUCTION



BLACK	4/6 NYLON, V2	1 520961-4
NATURAL	6/6 NYLON, V2	520961-3
NATURAL	66/6 NYLON, V0	1 520961-2
BLACK	6/6 NYLON, V2	520961-1
FINISH- COLOR	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 1/5/89	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK MS FEHER 1/5/89				
		APVD J GILLESPIE 3/7/89				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC				
0 PLC ± -		APPLICATION SPEC	NAME HOUSING, POSITIVE- LOCK, .250 SERIES, MK I			
1 PLC ± -		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=520961	RESTRICTED TO -
2 PLC ± -		CUSTOMER DRAWING				
3 PLC ± .010		SCALE 4:1				
4 PLC ± -		SHEET 1 of 1				
ANGLES ± -		REV R1				
FINISH						
SEE TABLE						
SEE TABLE						