


GR281 (2K x 8) NON-VOLATILE RAM

GREENWICH
INSTRUMENTS LTD



DESCRIPTION

The GR281 is a 2048 word by 8 bits (2K x 8) non-volatile CMOS Static Ram, fabricated from advanced silicon gate CMOS technology and a high reliability lithium power cell.

The pin-out of the GR281 conforms to the JEDEC standards and is fully compatible with normal static RAM.

The power down circuit is fully automatic and is referenced at 4.5 volts. At this point the GR281 is write protected by an internal inhibit function for Data Protection and the memory contents are retained by the lithium power source.

Power down is very fast, this being essential for data integrity, taking a maximum of 15 μ S (15 microseconds) to power down from 5 volts to 0 volts. This is much faster than system power failure conditions. Therefore there are no special conditions required when installing the GR281.

The GR281 can, without external power, retain data almost indefinitely. The limiting factor will be the shelf life of the lithium cell, which is typically ten years. It is possible that this figure may be extended in view of the extremely light duty imposed upon the cell.

APPLICATION

When powered down, the GR281 is transportable and data can be moved from system to system. Being pin compatible with 2716 EPROM makes it ideal for programme development, data collection in data loggers, programme changes in process control, automation and robotics and user definable lookup tables, etc.

DISPOSAL INSTRUCTIONS

Do not dispose of non-volatile memory devices by incineration or crushing. Devices may be returned carriage paid to Greenwich Instruments Ltd., for disposal.

UK

Greenwich Instruments Ltd.,
Meridian House, Park Road,
Swanley, Kent. BR8 8AH
Tele: 08700 505 404
Fax: 08700 505 405

ABSOLUTE MAXIMUM RATINGS

Symbol	Min	Max	Units
Vdd	-0.3	7.0	Volts
Vi/o	-0.3	Vdd +0.3	Volts
Temp	-20	+70	deg. C

OPERATING CONDITIONS

Symbol	Min	Typ	Max	Unit
Vdd	4.75	5.0	5.5	Volts
Vin (1)	2.2		Vdd+0.3	Volts
Vin (0)	-0.3		0.8	Volts
Iin (any other pin)	-1.0		+1.0	μ A.
Vout (1)(Iout = -1mA)	2.4			Volts
Vout (0)(Iout = +2mA)			0.4	Volts
Idd (Active)		25		mA.
Idd (Deselected)		1.0		mA.
Tcycle			100	nS.
Cin (any pin)			10	pF

OPERATING MODE

CE	OE	WR	MODE	OUTPUT	Idd
H	X	X	Unsel.	Hi-Z	Standby
L	H	H	Unsel.	Hi-Z	Active
L	L	H	Read	Dout	Active
L	X	L	Write	Din	Active


PIN CONNECTIONS

A7	1	24	Vdd
A6	2	23	A8
A5	3	22	A9
A4	4	21	WR
A3	5	20	OE
A2	6	19	A10
A1	7	18	CE
A0	8	17	D7
D0	9	16	D6
D1	10	15	D5
D2	11	14	D4
GND	12	13	D3

PIN DESIGNATIONS

Pin	Function
A0-A10	Address I/P's
D0-D7	Data in/out
OE	Output Enable
CE	Chip Enable
WR	Write Input
Vdd	+5Volt Power
GND	Ground


DATA RETENTION OPERATING CONDITIONS



Symbol	Parameter	Min	Typ	Max	Units
Vdd	Operating supply voltage	4.75	5.0	5.50	Volts
VTH	Data retention voltage		4.5		Volts
tF	Vdd slew to 0V	15			μ S
tR	Vdd slew 0V to 5.0V	15			μ S
tREC	CE to O/P valid from power up			15	μ S
tDR	Data retention time		10		Years
tPD	CE at Vin(1) before power down	0			μ S

GR281 (2K x 8) NON-VOLATILE RAM

GREENWICH
INSTRUMENTS LTD



DESCRIPTION

The GR281 is a 2048 word by 8 bits (2K x 8) non-volatile CMOS Static Ram, fabricated from advanced silicon gate CMOS technology and a high reliability lithium power cell.

The pin-out of the GR281 conforms to the JEDEC standards and is fully compatible with normal static RAM.

The power down circuit is fully automatic and is referenced at 4.5 volts. At this point the GR281 is write protected by an internal inhibit function for Data Protection and the memory contents are retained by the lithium power source.

Power down is very fast, this being essential for data integrity, taking a maximum of 15 μ S (15 microseconds) to power down from 5 volts to 0 volts. This is much faster than system power failure conditions. Therefore there are no special conditions required when installing the GR281.

The GR281 can, without external power, retain data almost indefinitely. The limiting factor will be the shelf life of the lithium cell, which is typically ten years. It is possible that this figure may be extended in view of the extremely light duty imposed upon the cell.

APPLICATION

When powered down, the GR281 is transportable and data can be moved from system to system. Being pin compatible with 2716 EPROM makes it ideal for programme development, data collection in data loggers, programme changes in process control, automation and robotics and user definable lookup tables, etc.

DISPOSAL INSTRUCTIONS

Do not dispose of non-volatile memory devices by incineration or crushing. Devices may be returned carriage paid to Greenwich Instruments Ltd., for disposal.

UK

Greenwich Instruments Ltd.,
Meridian House, Park Road,
Swanley, Kent. BR8 8AH
Tele: 08700 505 404
Fax: 08700 505 405

ABSOLUTE MAXIMUM RATINGS

Symbol	Min	Max	Units
Vdd	-0.3	7.0	Volts
Vi/o	-0.3	Vdd +0.3	Volts
Temp	-20	+70	deg. C

OPERATING CONDITIONS

Symbol	Min	Typ	Max	Unit
Vdd	4.75	5.0	5.5	Volts
Vin (1)	2.2		Vdd+0.3	Volts
Vin (0)	-0.3		0.8	Volts
Iin (any other pin)	-1.0		+1.0	μ A.
Vout (1)(Iout = -1mA)	2.4			Volts
Vout (0)(Iout = +2mA)			0.4	Volts
Idd (Active)		25		mA.
Idd (Deselected)		1.0		mA.
Tcycle			100	nS.
Cin (any pin)			10	pF

OPERATING MODE

CE	OE	WR	MODE	OUTPUT	Idd
H	X	X	Unsel.	Hi-Z	Standby
L	H	H	Unsel.	Hi-Z	Active
L	L	H	Read	Dout	Active
L	X	L	Write	Din	Active


PIN CONNECTIONS

A7	1	24	Vdd
A6	2	23	A8
A5	3	22	A9
A4	4	21	WR
A3	5	20	OE
A2	6	19	A10
A1	7	18	CE
A0	8	17	D7
D0	9	16	D6
D1	10	15	D5
D2	11	14	D4
GND	12	13	D3

PIN DESIGNATIONS


Pin	Function
A0-A10	Address I/P's
D0-D7	Data in/out
OE	Output Enable
CE	Chip Enable
WR	Write Input
Vdd	+5Volt Power
GND	Ground

DATA RETENTION OPERATING CONDITIONS




Symbol	Parameter	Min	Typ	Max	Units
Vdd	Operating supply voltage	4.75	5.0	5.50	Volts
VTH	Data retention voltage		4.5		Volts
tF	Vdd slew to 0V	15			μ S
tR	Vdd slew 0V to 5.0V	15			μ S
tREC	CE to O/P valid from power up			15	μ S
tDR	Data retention time		10		Years
tPD	CE at Vin(1) before power down	0			μ S

GR281 (2K x 8) NON-VOLATILE RAM




TIMING (nS-nano seconds)

Symbol	Parameter	100nS	Min	Max
tRC	Read cycle time	100		
tACC	Access time		100	
tACS	CE to output valid		100	
tOE	OE to output valid		40	
tCLZ	CE to output active	10		
tOLZ	OE to output active	10		
tOH	Output hold time	10		
tCHZ	CE to output disable		40	
tOHZ	OE to output disable		40	





Symbol	Parameter	100nS	Min	Max
tWC	Write cycle time	100		
tWP	Write pulse width	60		
tAS	Address setup time	0		
tWR	Write recovery time	10		
tWHZ	WR to output disable		30	
tOW	Output active from WR	10		
tDS	Data setup time	30		
tDH	Data HOLD TIME	10		



- Notes
1. WE must be high during address transitions.
 2. A Write occurs during the overlap of active CE and a low WE.
 3. WE is high for a read cycle.

REPLACES
2016., 6116., 8416., 5517., 4016., 2128., 5128., PD446., 8128., 4802., 5116., etc.

DIMENSIONS (mm)




Greenwich Instruments Ltd., are continually developing their products and reserve the right to alter specifications without prior notice. Standard Terms and Conditions of Sale apply.

<http://www.greenwichinst.co.uk>


ISSUE 4 OCT 2005

GR281 (2K x 8) NON-VOLATILE RAM




TIMING (nS-nano seconds)

Symbol	Parameter	100nS	Min	Max
tRC	Read cycle time	100		
tACC	Access time		100	
tACS	CE to output valid		100	
tOE	OE to output valid		40	
tCLZ	CE to output active	10		
tOLZ	OE to output active	10		
tOH	Output hold time	10		
tCHZ	CE to output disable		40	
tOHZ	OE to output disable		40	





Symbol	Parameter	100nS	Min	Max
tWC	Write cycle time	100		
tWP	Write pulse width	60		
tAS	Address setup time	0		
tWR	Write recovery time	10		
tWHZ	WR to output disable		30	
tOW	Output active from WR	10		
tDS	Data setup time	30		
tDH	Data HOLD TIME	10		



- Notes
1. WE must be high during address transitions.
 2. A Write occurs during the overlap of active CE and a low WE.
 3. WE is high for a read cycle.

REPLACES
2016., 6116., 8416., 5517., 4016., 2128., 5128., PD446., 8128., 4802., 5116., etc.

DIMENSIONS (mm)



Greenwich Instruments Ltd., are continually developing their products and reserve the right to alter specifications without prior notice. Standard Terms and Conditions of Sale apply.

<http://www.greenwichinst.co.uk>

ISSUE 4 OCT 2005