


# LABFACILITY

## TEMPERATURE & PROCESS TECHNOLOGY

### Glass fibre Insulated Flat Pair Types 'K' 1/0.3 solid strand– to ANSI



- Glass fibre insulated extension cable in thermocouple type K
- Glass fibre insulated flat pair construction, conductors laid flat, Glass fibre insulated with Glass fibre overall, silicone varnished throughout
- Good temperature resistance but not suitable where fluids are present
- Available in solid 1/0.3mm conductors
- Available in 25, 50 or 100 metre reel lengths
- Conductors are made from associated K Thermocouple alloy type
- Tolerance Class 2 to ANSI MC96.1
- Insulation rating -60°C to 350°C (short periods up to 400°C)
- Colour code (cores & jacket) to ANSI MC96.1

T/C Type	Conductors	Cores	Jacket	Reel Length	Manufactures Code	Farnell Order Code
KX	1/0.3mm	+yellow/-red	Yellow	25m	WK-351-ANSI x 25m	244-3697
KX	1/0.3mm	+yellow/-red	Yellow	50m	WK-351-ANSI x 50m	244-3698
KX	1/0.3mm	+yellow/-red	Yellow	100m	WK-351-ANSI x 100m	244-3699

#### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

#### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

#### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com