

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F


E

D

C

B

A







PANEL THICKNESS RANGE
.10 TO .028
2.5 TO .71

BAYONET STYLE
LOCKING INTERFACE

.18
4.6
PANEL KEY

.56
14.2
PANEL KEY

- NOTES:
- 1. MATERIAL: SEE TABLE
 - 2. FINISHES: SEE TABLE
 - 3. PRODUCT SPECIFICATION: SEE SPECS
 - 4. PACKAGING: AS REQUIRED
 - 5. MATES WITH: INDUSTRY STANDARD
 - 6. FORMERLY SD-84702-0008.
 - 7. WIRING POLARIZATION & SEQUENCE PER EIA 568B.
 - 8. COMPATIBLE WITH SOLID AND STRANDED COPPER CONDUCTORS.
 - 9. CONDUCTOR RANGES ARE 22-26AWG WITH A MAX OF 7 STRANDS PER BUNDLE. LIMITING O.D. IS .055"
 - 10. CAN BE RETERMINATED UP TO 200 TIMES



9	A/R	POTTING COMPOUND (NOT SHOWN)	EPOXY	BLACK
8	2	STUFFER CAP (MPN #201-345)	THERMOPLASTIC	WHITE
7	1	PUNCHDOWN BLOCK	THERMOPLASTIC	WHITE
6	1	PUNCHDOWN BLOCK	THERMOPLASTIC	WHITE
5	1	PCB	FR-4	GREEN
4	1	PANEL GASKET	NEOPRENE	BLACK
3	1	RJ-45 JACK W/PCB MTG	POLYESTER	BLACK
2	1	LOCK NUT	POLYESTER	BLACK
1	1	RECEPTACLE HOUSING	POYESTER	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

ADDED NOTES 8.9.10
EC NO: ETC2006-0133
DRWNS:BRADLEY 2005/12/12
CHKD:RSTONE 2005/12/13
APPR:RDEROSS 2005/12/16

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .01	± .001
2 PLACES	± .013	± .0013
1 PLACE	± .013	± .0013

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY
S. GILBERT

DATE
03/07/30

CHECKED BY
P. WAITZ

DATE
03/11/20

APPROVED BY
GHR

DATE
04/03/08

MATERIAL NO.
847020008

SCALE
4:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

PANEL MTG. RECEPTACLE
RJ-45 PUNCHDOWN CIC
FULLY POTTED ETHERNET

MOLEX INCORPORATED

DOCUMENT NO.
SD-84702-005

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION