



Dimensions: In.

■ Specifications:

- Primary Voltage: 115VAC, 60Hz
- Primary Exciting Current: 40mA (max.)
- Secondary Voltage (no load): 20.6CT VAC \pm 0.6V%
- Secondary Voltage (full load): 18.0CT VAC \pm 0.6V%
- Rated Secondary Current: 0.3 Amp (AC) @ 60Hz
- Voltage Regulation: <15% (VNL-VFL)/(VFL)x100
- Temperature Rise (@ room temp. 25°C): <50°C
- Breakdown Voltage (HiPOT): 2000VAC @ 50Hz for 1 min
- Coil to Coil Insulation: 200M Ω (min.), 500VDC
- Strain Relief: 10 lbs.
- Channel Frame Material: 0.6mm Thick Iron
- Crossover Insulation: 0.05mm Thick Polyester Tape
- Primary Winding: SWG38 (0.15mm)
- Secondary Winding: SWG29 (0.35mm)
- Core Material and Size: HiLite Core H-23, 0.5mm Thick, EI-41
- Inner Insulation: 3 Layers of 0.05mm Polyester Tape
- Outer Wrap Insulation: 3 Layers of 0.05mm thick yellow Polyester Tape with 1 piece of Fiber Board
- Bobbin: Nylon, normal type, 13mm x 19.2mm
- Impregnation: Varnish
- Lead Wire: PRI-AWG22, SEC-AWG22

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

41FJ300