

ALUMILINE SLIM LED FIXTURE

Features


Long Life
Low Power Consumption
RoHS Compliant
No UV Emission
Thermally Optimized
Low Profile

Protected against Dust and Splashing Water
Mounting Holes for Ease of Installation
Available in Multiple LED Spacing
Warm to Cool Light Output
Custom Connectors Available
Low Voltage Operation

A DIM. ± 1.2mm (±.05 inch)	B DIM. mm (inch)	Power (W)	Current (mA)	Lumen Flux (lm)
310 (12.20)	10 (.40)	2.0	85	150
610 (24.00)	10 (.40)	4.1	170	300
910 (35.83)	10 (.40)	6.1	255	450
1210 (47.64)	10 (.40)	8.2	340	600

310 (12.20)	16.7 (.66)	1.2	51	90
610 (24.00)	16.7 (.66)	2.4	102	180
910 (35.83)	16.7 (.66)	3.7	153	270
1210 (47.64)	16.7 (.66)	4.8	201	360

310 (12.20)	25 (.98)	0.8	34	60
610 (24.00)	25 (.98)	1.6	68	120
910 (35.83)	25 (.98)	2.4	102	180
1210 (47.64)	25 (.98)	3.3	136	240



Part No. Ordering Guide

ZLF -	DIM. A	COLOR	OPTION	DIM. B	VOLTS
	XXXX /	XX	/ X	/ XX	- XX
	0310	W1 - 3500K	X	10 - 10mm	12
	0610	W3 - 5300K		16 - 16.7mm	24
	0910	W5 - 6000K		25 - 25mm	
	1210	W6 - 7500K			

 THIRD ANGLE PROJECTION	DIMENSIONS ARE MILLIMETER (INCH)		JKL COMPONENTS CORPORATION			
	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- REF.		TITLE ALUMILINE SLIM LED FIXTURE			
DRAWN BY L. WENGSTROM	APPVD BY L.R.	DATE 12/23/09	SIZE A	FSCM NO. 55335	DRAWING NO. ZLF-MULTI	
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		RELEASED DATE 12/23/09	REVISION DATE
				NONE		REV. NO. 1 OF 1