

EBR 6 Amp Epoxy Bridge Rectifiers VH Series


Glass Passivated Silicon Chips

Controlled Avalanche Series with 250V, 450V, 650V, and 850V Minimum Avalanche Ratings

Non-controlled Avalanche Series with 50V, 100V, 200V, 400V, 600V, 800V, and 1000V V_{RRM} Ratings

100 Amps Peak One Half Cycle Surge Current

LTR.	INCHES	MILLIMETERS
A	.411-.441	10.44-11.20
B	.590-.610	14.99-15.49
C	.137-.167 Dia.	3.48-4.24 Dia.
D	.295-.305	7.49-7.75
E	.037-.043 Dia.	.94-1.09 Dia.
F	1.0 Min.	25.4 Min.
G	.195-.205	4.95-5.21



MAXIMUM RATINGS (At $T_A = 25^\circ\text{C}$ unless otherwise specified)

RATINGS	SYMBOL	CONTROLLED AVALANCHE				NON-CONTROLLED AVALANCHE							UNITS
Series Number		VH247	VH447	VH647	VH847	VH048	VH148	VH248	VH448	VH648	VH848	VH1048	
DC Blocking Voltage Working Peak Reverse Voltage Peak Repetitive Reverse Voltage	V_{RM} V_{RWM} V_{RRM}	200	400	600	800	50	100	200	400	600	800	1000	Volts
RMS Reverse Voltage	$V_{R(RMS)}$	140	280	420	560	35	70	140	280	420	560	700	Volts
Power Dissipation in V_{RRM} Region for 100 μ SEC Square Wave	P_{RM}	400				NA							Watts
Continuous Power Dissipation in V_{RRM} Region at $T_{HS} = 80^{\circ}$ C	P_R	2				NA							Watts
Fusing Data	I^2t					40							Amps ² Sec.
Peak Surge Current, 1/2 Cycle at 60 Hz, (Non-Rep) at $T_{HS} = 80^{\circ}$ C (Fig. 2)	I_{FSM}					100							Amps
Peak Surge Current, 1 sec. at 60 Hz and $T_{HS} = 80^{\circ}$ C (Fig. 2)	I_{FRM}					25							Amps
Avg. Forward Current at $T_{HS} = 80^{\circ}$ C (Fig. 1)	I_O					6							Amps
Junction Operating and Storage Temperature Range	T_J, T_{STG}					- 50 to + 150							$^{\circ}$ C
Maximum soldering temperature and time						10 Sec at 265 $^{\circ}$ C							

ELECTRICAL CHARACTERISTICS (At $T_A = 25^\circ\text{C}$ unless otherwise noted)

RATINGS	SYMBOL	CONTROLLED AVALANCHE				NON-CONTROLLED AVALANCHE						UNITS	
Series Number		VH247	VH447	VH647	VH847	VH048	VH148	VH248	VH448	VH648	VH848	VH1048	
Minimum Avalanche Voltage	V _{BR}	250	450	650	850	NA						Volts	
Maximum Avalanche Voltage	V _{BR}	700	900	1100	1300	NA						Volts	
Maximum Instantaneous Forward Voltage Drop (Per Diode) at 6 Amps (Fig. 3)	V _{FM}	1.3										Volts/ Leg	
Maximum Reverse Current at Rated V _{RM}	I _{RM}	5										μA	
Maximum Reverse Current at Rated V _{RM} at T _J = 125°C	I _{RM}	1.0										mA	
Insulation Strength From Circuit to Case (min.)		2000										Volts DC	
Thermal Resistance (Typ.) Junction to case (on heat sink) Junction to air (no heat sink)	R _{JJC} R _{JJA}	6 25										°C/W °C/W	

Part Nos. VH247, VH447, VH647, VH847, VH048, VH148, VH248, VH448, VH648, and VH848 have been recognized under the Component Program of Underwriters Laboratories, Inc.




FIGURE 1




FIGURE 2

T-23-07




FIGURE 3




FIGURE 4




FIGURE 5




FIGURE 6