






INTERCONNECTS

SERIES 714...00X • .100" GRID LOW PROFILE CARRIERS • SINGLE AND DOUBLE ROW STRIPS



- Low profile receptacles sit .031" above the board
- Series 714 use MM #1401 and MM #1407 pin receptacles. See pages 157 and 170 for details
- Hi-Rel, 4-finger BeCu #30 contact is used in the #1401 receptacle and a BeCu #11 contact is used in the #1407. Both contacts are rated at 3 amps. See pages 251 and 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Single Row (.055" min. mounting hole)					
	714-XX-1	-41-001000	Specify number of pins	01-64		
FIG. 2	Single Row (.039" min. mounting hole)					
	714-XX-1	-31-007000	Specify number of pins	01-64		
FIG. 3	Double Row (.055" min. mounting hole)					
	714-XX-2	-41-001000	Specify number of pins	04-64		
FIG. 4	Double Row (.039" min. mounting hole)					
	714-XX-2	-31-007000	Specify number of pins	04-64		
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264						
SPECIFY PLATING CODE XX=		91	93	41	43	
Sleeve (Pin)		200 μ"Sn/Pb	200 μ"Sn/Pb	200 μ"Sn	200 μ"Sn	
Contact (Clip)		10 μ"Au	30 μ"Au	10 μ"Au	30 μ"Au	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[714-93-264-41-001000](#) [714-93-264-31-007000](#) [714-93-164-41-001000](#) [714-93-164-31-007000](#) [714-93-120-41-001000](#) [714-93-120-31-007000](#) [714-93-110-31-007000](#) [714-93-132-41-001000](#) [714-93-106-31-007000](#) [714-93-132-31-007000](#) [714-43-264-41-001000](#) [714-43-264-31-007000](#) [714-43-164-41-001000](#) [714-43-164-31-007000](#) [714-43-132-41-001000](#) [714-43-132-31-007000](#) [714-43-120-41-001000](#) [714-43-120-31-007000](#)