




REV.	DATE	DESCRIPTION
NC	03/06/00	INITIAL RELEASE




RECOMMENDED
CABLE STRIPPING DIM'S





RECOMMENDED
MOUNTING HOLE



6 HEX NUT



ø7.8 [ø.307]
ø5 [ø.197]



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .151"

	DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE						
1	BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	DRAWN	G.R.S.	03/06/00	TITLE BULKHEAD CABLE TERMINATION (FOR RG-316 DOUBLE BRAID CABLE)				
2	FERRULE	COPPER	NICKEL		CHECKED							
3	LOCK WASHER	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	ISSUED		SIZE		FSCM NO.	DWG. NO.	REV.	
4	HEX NUT	BRASS	NICKEL				A	99001	142274.DWG		NC	
5												
6												
7												
8				DO NOT SCALE DRAWING			SCALE	NA	PART NO.	142274	SHEET	1 OF 1