

9	HEX NUT	BRASS	NEXCOTE	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex						
8	LOCK WASHER	BRASS	NEXCOTE	1		DRAWN	M.ZHANG					07/30/09	PART DESCRIPTION N BULKHEAD DIRECT SOLDER JACK (FOR .085",.086" CABLE)	
7	GASKET	SILICONE	RED	1		CHECKED			PART NO. 172138					
6	SOLDER NUT	BRASS	GOLD	1		ISSUED							DWG. NO. 172138.DWG	
5	INSULATOR	PTFE	NATURAL	1		SHEET	1 OF 1		REV.	NC	SIZE	A		
4	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1										
3	INNER BODY	BRASS	NEXCOTE	1										
2	INSULATOR	PTFE	NATURAL	1										
1	OUTER BODY	BRASS	NEXCOTE	1										
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/CONNEX/172138.DWG								