


Types D, E, F, FM, 2F, F9, interface connectors I/U


Page

Technical characteristics types D and E **02.10**

Type D connectors **02.11**




Type E connectors **02.15**




Technical characteristics piggyback connectors **02.20**

Piggyback connectors **02.21**



Technical characteristics types F, F9, FM and 2F **02.24**


Type F connectors **02.25**




Type F9 connectors **02.35**



Type FM connectors **02.36**



Type 2F connectors **02.38**



Coding systems **02.41**

Number of contacts

Type D	32
Type E	48

Contact spacing (mm)

Type D	5,08	
Type E	male connector	5.08 x 5.08
	male connector	2.54 x 5.08
	female connector	5.08 x 5.08

Working current

6 A max.
see current carrying capacity chart

Clearance

Types D und E	≥ 3.0 mm
Type E male connector row separation 2.54 mm	≥ 1.6 mm

Creepage

≥ 3.0 mm

Working voltage

The working voltage also depends on the clearance and creepage dimensions of the pcb itself and the associated wiring according to the safety regulations of the equipment
Explanations see chapter 00

Test voltage $U_{r.m.s.}$

1.55 kV

Contact resistance

≤ 15 mΩ for wire wrap and solder connections
≤ 20 mΩ including crimp connections

Insulation resistance

≥ 10¹² Ω

Temperature range

– 55 °C ... + 125 °C

The higher temperature limit includes the local ambient and heating effects of the contacts under load

Degree of protection for crimp terminal IP 20
according to DIN 40 050

Electrical termination

Male connector	Solder pins for pcb connections Ø 1.0 ± 0.1 mm according to IEC 60 326-3 Wrap posts 1 x 1 mm diagonal 1.34-1.45 mm
Female connector	Solder pins for pcb connections Ø 1.0 ± 0.1 mm according to IEC 60 326-3 Angled solder pins 1 x 1 mm for pcb connections Ø 1.6 ± 0.1 mm Solder lugs Crimp terminal 0.09-1.5 mm ²

Insertion and withdrawal force

32 way ≤ 40 N
48 way ≤ 75 N

Materials

Mouldings	Thermoplastic resin, glass-fibre filled, UL 94-V0
Contacts	Copper alloy

Contact surface

Contact zone	Selectively gold plated according to performance level ¹⁾
--------------	--


¹⁾ Explanation of performance levels see chapter 00

Mating conditions	see chapter 00
Coding systems	see pages 02.41 and 02.42
Mounting clips	see chapter 00

Current carrying capacity

The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60 512




Fitting the crimp contacts

After crimping the wires onto the contacts with the help of a crimping tool or an automatic crimping machine the contacts should be correctly oriented and inserted into the cavities of the connector moulding in the required configuration. They snap into position and are firmly held in place. A light pull on the wire assures the correct tensile strength of the contact. When using stranded wires with a gauge below 0.37 mm² an insertion tool is necessary.

Removing the crimp contacts

The removal tool is inserted into a slot on the side of the respective crimp cavity. This action compresses the contact retaining spring therefore the contact can then be easily withdrawn using a light pull on the wire. This action will cause no damage to the contact/wire which can be repositioned/refitted as necessary. The drawing demonstrates the crimp removal procedure (max. 5x).



Number of contacts

32



Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00		
			3	2	1	
Male connector with angled solder pins	32		09 04 132 7921	09 04 132 6921 09 04 332 6921 ^{b)} 09 04 632 6921 ^{c)}	09 04 132 2921	
	30 + 2▲			09 04 132 6951 09 04 632 6951 ^{c)}	09 04 632 2951 ^{c)}	
Male connector with straight solder pins	32			09 04 132 6922		
	30 + 2▲			09 04 132 6952		
Dimensions						
Board drillings Mounting side						

Dimensions in mm

Dimensions in mm


▲ Male connectors with 2 leading contacts [(0.8 mm) pos. a2 and a32]

Other contact arrangements on request

^{b)} Connectors with snap-in clips see chapter 00

^{c)} Connectors with coding see page 02.42

32



Female connectors

			Part No.	Performance levels according to IEC 60 603-2. Explanation chapter 00	
Identification	Number of contacts	Contact arrangement	3	2	1
Female connector with solder pins 2.9 mm	32		09 04 232 7832	09 04 232 6832 09 04 732 6832 ^{c)}	09 04 232 2832
Female connector with solder pins 4.5 mm	32		09 04 232 7831	09 04 232 6831 09 04 332 6831 ^{b)} 09 04 732 6831 ^{c)}	09 04 232 2831
Female connector with wrap posts 20 mm	32		09 04 232 7821	09 04 232 6821 09 04 732 6821 ^{c)}	09 04 232 2821
Female connector with solder lugs	32		09 04 232 7823	09 04 232 6823	09 04 232 2823

Solder pins

a
2.9
4.5

Wrap posts

a	b
20	1

Solder lugs

a	b	c
2.9	1.1	0.8
4.5	1.1	0.8

Contact arrangement

View from termination side

Technical drawing showing dimensions and contact arrangement for a PCB layout. The drawing includes a top view and a side view.

Top View Dimensions:

- Overall width: 95.5
- Internal width: 90 ± 0.1
- Internal width: 85
- Mounting holes: M2.5 / $\phi 2.8$
- Internal dimensions: 51, 10.8, 51, 12.7

Side View Dimensions:

- Overall height: 0.3
- Internal height: 1 ± 0.1
- Internal height: 5.08
- Internal height: 15 x 5.08 (=76.20)
- Internal height: 9.0
- Internal height: 8.17
- Internal height: 2.54
- Internal height: 5.08
- Internal height: 2.8 ± 0.1
- Internal height: 2x

Contact Arrangement:

- all holes
- 2c
- 2a
- 32

Board drillings
Mounting side

Dimensions in mm

Number of contacts

32



Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00		
			3	2	1	
Female connector with angled solder pins 1 x 1 mm	32		09 04 232 7826	09 04 232 6826	09 04 232 2826	
Dimensions						
Fixing bracket Metal			09 06 000 9912 ¹⁾			
Board drillings Mounting side						


¹⁾ order 2 pieces for one connector

Dimensions in mm

DIN Power
to 6 A

Number of contacts

max. 32



Female connectors

DIN Power
to 6 A

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately	32	09 04 032 3213		
Shell housing 09 03 096 0501 see chapter 20				

Identification	Identification Wire gauge	Part No.	Performance levels according to IEC 60 603-2. Explanation chapter 00	
			2	1
Female crimp FC contacts				
Bandoliered contacts (approx. 2,500 pieces)	1	09 06 000 6484	09 06 000 6474	
	2	09 06 000 6481	09 06 000 6471	
	3	09 06 000 6482	09 06 000 6472	
Bandoliered contacts (approx. 250 pieces)	1	09 06 000 7484	09 06 000 7474	
	2	09 06 000 7481	09 06 000 7471	
	3	09 06 000 7482	09 06 000 7472	
Individual contacts ¹⁾	1	09 06 000 8484	09 06 000 8474	
	2	09 06 000 8481	09 06 000 8471	
	3	09 06 000 8482	09 06 000 8472	
Female contacts with solder lugs ²⁾ (lockable)			09 06 000 6420	

		Wire gauge mm ²	AWG	Insulation ø mm	Identification
FC 1 FC 2 FC 3	1	0.09 - 0.25	28 - 24	0.7 - 1.5	
	2	0.14 - 0.56	26 - 20	0.8 - 2.0	
	3	0.5 - 1.5	20 - 16	1.6 - 2.8	
3.5 + 0.5 mm of insulation is stripped from the wires to be crimped					Bandoliered contacts
Insertion, removal and crimping tools see chapter 30					Individual contacts

¹⁾ Packaging unit 1,000 pieces

²⁾ Solder contacts must not be used together with shell housing A. Special contact surface: 2 µm gold.

Number of contacts

48




Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2. Explanation chapter 00	
			3	2	1
Male connector with angled solder pins					
Row separation termination side 5.08 mm ①	48		09 05 148 7921	09 05 148 6921 09 05 348 6921 ^{b)} 09 05 648 6921 ^{c)}	09 05 148 2921 09 05 648 2921 ^{c)}
	46 + 2 [▲]			09 05 148 6951	
Row separation termination side 2.54 mm ②	48		09 05 148 7931	09 05 148 6931	09 05 148 2931
	46 + 2 [▲]			09 05 148 6961	


DIN Power
to 6 A

Dimensions



Board drillings

Mounting side



Dimensions in mm

▲ Male connectors with 2 leading contacts [(0.8 mm) pos. a2 and a32]


Other contact arrangements on request

^{b)} Connectors with snap-in clips see chapter 00

^{c)} Connectors with coding see page 02.42

Number of contacts

48




Interface connector I

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Interface connector I with solder pins 0.6 x 0.6 mm	48	Performance level 2 acc. to IEC 60 603-2 09 05 048 6924	 Contact arrangement View from termination side 	 Board drillings Mounting side

DIN Power
to 6 A

Number of contacts

48



Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00													
			3	2	1												
Female connector with solder pins 2.9 mm	48		09 05 248 7832	09 05 248 6832	09 05 248 2832												
Female connector with solder pins 4.5 mm	48		09 05 248 7831	09 05 248 6831 09 05 348 6831 ^{b)} 09 05 748 6831 ^{c)}	09 05 248 2831 09 05 748 2831 ^{c)}												
Female connector with wrap posts 20 mm	48		09 05 248 7821	09 05 248 6821	09 05 248 2821												
Female connector with solder lugs	48		09 05 248 7823	09 05 248 6823	09 05 248 2823												
Female connector with press-in pins	Part Nos. and variants see chapter 04																
Dimensions	<table><tr><td>a</td><td>2.9</td><td>Solder pins</td></tr><tr><td>a</td><td>4.5</td><td></td></tr><tr><td>a</td><td>20</td><td>Wrap posts</td></tr><tr><td>b</td><td>1</td><td></td></tr></table> Solder lugs					a	2.9	Solder pins	a	4.5		a	20	Wrap posts	b	1	
a	2.9	Solder pins															
a	4.5																
a	20	Wrap posts															
b	1																
Panel cut out	Contact arrangement View from termination side																
Board drillings Mounting side																	

Dimensions in mm


DIN Power
to 6 A

Dimensions in mm

^{b)} Connectors with snap-in clips see chapter 00
^{c)} Connectors with coding see page 02.42

Number of contacts

max. 48



Female connectors

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately	48	09 05 048 3202 09 05 548 3202 ^{c)}	View from termination side	
Shell housing 09 05 048 0501 see chapter 20				

Identification	Identification Wire gauge	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00
Female crimp FC contacts			2
Bandoliered contacts (approx. 2,500 pieces)	1	09 06 000 6484	09 06 000 6474
	2	09 06 000 6481	09 06 000 6471
	3	09 06 000 6482	09 06 000 6472
Bandoliered contacts (approx. 250 pieces)	1	09 06 000 7484	09 06 000 7474
	2	09 06 000 7481	09 06 000 7471
	3	09 06 000 7482	09 06 000 7472
Individual contacts ¹⁾	1	09 06 000 8484	09 06 000 8474
	2	09 06 000 8481	09 06 000 8471
	3	09 06 000 8482	09 06 000 8472
Female contacts with solder lugs ²⁾ (lockable)			09 06 000 6420

FC 1
FC 2
FC 3

1
2
3

Wire gauge
mm²


AWG

Insulation ø
mm

Identification

Bandoliered
contacts


Individual contacts



3.5 + 0.5 mm of insulation is stripped from the wires to be crimped

Insertion, removal and crimping tools see chapter 30

^{c)} Connectors with coding see page 02.42¹⁾ Packaging unit 1,000 pieces²⁾ Solder contacts must not be used together with shell housing A. Special contact surface: 2 µm gold.



DIN Power
to 6 A



Our claim is quality.

Simultaneous and fully automated high-speed stamping of several contacts with small tolerances.

Number of contacts 16, 32, 48

Working current 6 A max.
see current carrying capacity chart

Clearance

16 ways ≥ 1.6 mm
32, 48 ways ≥ 1.6 mm

Creepage

16 ways ≥ 1.6 mm
32, 48 ways ≥ 3.0 mm

Working voltage

The working voltage also depends on the clearance and creepage dimensions of the pcb itself and the associated wiring according to the safety regulations of the equipment
Explanations see chapter 00

Contact resistance ≤ 20 m Ω

Insulation resistance $\geq 10^{12}$ Ω

Termination Crimp terminal
0.09-1.5 mm²

Materials

Mouldings and hoods Thermoplastic resin,
glass-fibre filled
Contacts Copper alloy

Piggyback connectors for interfacing with female connectors with wrap posts 1 x 1 mm

The problem of interfacing systems designed for the distribution or collection of electronic signals can be overcome by the use of piggyback connectors. Designed to be mounted on the rear of DIN 41 612 type wire wrap female connectors (1 x 1 mm posts) these piggyback elements can be used to terminate input and output cables.

Distance fixing brackets are fitted to provide either a latching or screw fixing facility over the two level wire wrap plane.

The female crimp contacts used in these versions are designed for 1 x 1 mm posts.


After crimping they can be easily inserted into the chambers of the connector body with the aid of an insertion tool. Insertion errors can be simply rectified with the use of a removal tool.

2 and 3 row piggyback connectors can be mounted in shell housings C and open hood G. Security is provided by either latches or screws to the distance fixing brackets.


Current carrying capacity

The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60 512



① with shell housing ② without shell housing



Piggyback connectors




Number of contacts

max. 48


III



I



II



IV



Piggyback connectors for 1 x 1 mm wrap posts

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm																
Piggyback connector for crimp contacts Order contacts separately	16	09 04 016 3201																		
I	32	09 04 032 3215																		
II	48	09 05 048 3204																		
Female FC crimp contacts individual contacts¹⁾ Bandoliered contacts (approx. 2,500 pcs.)	FC1 FC2 FC3 FC1 FC2 FC3	09 06 000 6464 09 06 000 6461 09 06 000 6462 09 06 000 6454 09 06 000 6451 09 06 000 6452	<table><tr><th>Identi- fication</th><th>Wire gauge mm²</th><th>AWG</th><th>Insulations ø mm</th></tr><tr><td>1</td><td>0.09-0.25</td><td>28-24</td><td>0.7-1.5</td></tr><tr><td>2</td><td>0.14-0.56</td><td>26-20</td><td>0.8-2.0</td></tr><tr><td>3</td><td>0.50-1.50</td><td>20-16</td><td>1.6-2.8</td></tr></table>	Identi- fication	Wire gauge mm ²	AWG	Insulations ø mm	1	0.09-0.25	28-24	0.7-1.5	2	0.14-0.56	26-20	0.8-2.0	3	0.50-1.50	20-16	1.6-2.8	Identification
Identi- fication	Wire gauge mm ²	AWG	Insulations ø mm																	
1	0.09-0.25	28-24	0.7-1.5																	
2	0.14-0.56	26-20	0.8-2.0																	
3	0.50-1.50	20-16	1.6-2.8																	
Mateable with 1 x 1 mm wrap posts			3.5 + 0.5 mm of insulation is stripped from the wires to be crimped. Crimping tools see chapter 30																	
Distance fixing bra- ckets for female con- nectors Type D Type E		top (pos. 2) 09 04 000 9907 bottom (pos. 32) 09 04 000 9906																		
Type F	III IV	top (pos. 2) 09 06 000 9936 bottom (pos. 32) 09 06 000 9937																		

DIN Power to 6 A

¹⁾ Packaging unit 1,000 pieces

Identification





Drawing

Dimensions in mm

Mounting examples
of piggyback
connectors

without housings

with housings



¹ Number of contacts piggyback connector

² Doesn't belong to the scope of supply



Number of contacts

Type F	48, 32
Type FM	45
Type 2F	max. 24
Type F9	max. 9

Contact spacing (mm) 5.08

Working current 6 A max.
see current carrying capacity chart

Clearance ≥ 1.6 mm

Creepage ≥ 3.0 mm

Working voltage

The working voltage also depends on the clearance and creepage dimensions on the pcb itself and the associated wiring according to the safety regulations of the equipment
Explanations see chapter 00

Test voltage $U_{r.m.s.}$ 1.55 kV (contact-contact)
2.5 kV (contact-ground)

Contact resistance ≤ 15 m Ω for wire wrap and solder connections
 ≤ 20 m Ω including crimp connections

Insulation resistance $\geq 10^{12}$ Ω

Temperature range -55 $^{\circ}\text{C}$... $+125$ $^{\circ}\text{C}$

The higher temperature limit includes the local ambient and heating effects of the contacts under load

Electrical termination

Male connector	Solder pins for pcb connections $\varnothing 1 \pm 0.1$ mm according to IEC 60 326-3 Wrap posts 1 x 1 mm diagonal 1.34-1.45 mm Crimp terminal 0.09-1.5 mm ²
Female connector	Wrap posts 1 x 1 mm diagonal 1.34-1.45 mm Solder pins for pcb connections $\varnothing 1 \pm 0.1$ mm according to IEC 60 326-3 Angled solder pins 1 x 1 mm for pcb connections $\varnothing 1.6 \pm 0.1$ mm Solder lugs Crimp terminal 0.09-1.5 mm ²
Distributor	Crimp terminal 0.09-1.5 mm ²

Insertion and withdrawal force
48 way ≤ 75 N
45 way ≤ 70 N
32 way ≤ 50 N
24 way ≤ 37 N

Materials

Mouldings Thermoplastic resin, glass-fibre filled, UL 94-V0
Contacts Copper alloy

Contact surface

Contact zone Selectively plated according to performance level¹⁾


¹⁾ Explanation of performance levels see chapter 00

Mating conditions see chapter 00
Coding systems see pages 02.41 and 02.42
Mounting clips see chapter 00

Current carrying capacity

The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60 512




Fitting the crimp contacts


After crimping the wires onto the contacts with the help of a crimping tool or an automatic crimping machine the contacts should be correctly oriented and inserted into the cavities of the connector moulding in the required configuration. They snap into position and are firmly held in place. A light pull on the wire assures the correct tensile strength of the contact. When using stranded wires with a gauge below 0.37 mm² an insertion tool is necessary.

Removing the crimp contacts

The removal tool is inserted into a slot on the side of the respective crimp cavity. This action compresses the contact retaining spring therefore the contact can then be easily withdrawn using a light pull on the wire. This action will cause no damage to the contact/wire which can be repositioned/refitted as necessary. The drawing demonstrates the crimp removal procedure (max. 5x).



48, 32




Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00		
			3	2	1	
Male connector with angled solder pins ¹⁾	48		09 06 148 7901	09 06 148 6901 09 06 348 6901 ^{b)}	09 06 148 2901	
	32		09 06 132 7901 09 06 332 7901 ^{b)}	09 06 132 6901	09 06 132 2901	
	32		09 06 132 7931	09 06 132 6931 09 06 332 6931 ^{b)}	09 06 132 2931	
1 leading contact (position z 32)	47 + 1			09 06 148 6921 09 06 348 6921 ^{b)}	09 06 148 2921	
	31 + 1		09 06 132 7921	09 06 132 6921	09 06 132 2921	
2 leading contacts (positions b 2 + b 32)	46 + 2			09 06 148 6925	09 06 148 2925	

[illegible]

Technical drawing of a 15-hole punch plate. The main view shows a rectangular plate with 15 holes. The holes are arranged in a single row with a pitch of 5.08 mm. The total length of the hole row is 76.20 mm. The plate has a thickness of 2.54 mm. The distance from the center of the first hole to the left edge is 2.8 mm. The distance from the center of the last hole to the right edge is 7.62 mm. The total length of the plate is 88.9 mm. The drawing includes three cross-sections: d+b+z, b+z, and d+z, showing the internal structure of the plate and the holes.

Number of contacts

48, 32




Interface connectors I

Identification	Number of contacts	Contact arrangement	Part No.	Drawing	Dimensions in mm
Interface connector I with solder pins ¹⁾ 0.6 x 0.6 mm			Performance level 1*		
	48		09 06 048 2905		
	32		09 06 032 2905		
	32		09 06 032 2941		
Board drillings Mounting side					
Interface connector I with wrap posts ¹⁾ 1 x 1 mm			Performance level 1*		
	without nut		09 06 048 2903		
	with nut		09 06 048 2963		
	without nut		09 06 032 2903		
	with nut		09 06 032 2963		
Panel cut out					

* Acc. to IEC 60 603-2, performance level 2 on request

¹⁾ With shroud coding, see also page 02.41

48




Interface connector I

**DIN Power
to 6 A**

Number of contacts

48




Interface connector U

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Interface connector U with wrap posts 1 x 1 mm	48	Performance level 1 acc. to IEC 60 603-2 09 06 048 2981	Technical drawing of the connector showing side and top views with dimensions. The side view includes dimensions: 3+0.2, 2, 12.5, 15x5.08=76.20, 101+0.2, 106.5-0.2, 15.24, 6.8, 22, 14.8, 15.2, 2x5.08=10.16, 3.2+0.1, 31.9+0.3, 17.24, 1, 1. The top view shows contact arrangement with dimensions: 94, 90, 90, 8.17, 8.17, 0.3, 0.3.	
Mounting example			Technical drawing of the connector showing mounting example with dimensions. The drawing includes dimensions: 0.3, 5.08, M 3 x 8 DIN EN ISO 1207, 8.17, 17.23, 10.16, 90+0.1, 5.63, 5.08, 14.69, 2.4, M 2.5 x 6 DIN EN ISO 1207, A-B.	

Number of contacts

max. 48



Female connectors

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts¹⁾ Order contacts separately	48	09 06 248 3201	 Contact arrangement View from termination side	
Shell housing see chapter 20				

**DIN Power
to 6 A**

Identification	Identification Wire gauge	Part No.	Performance levels according to IEC 60 603-2. Explanation chapter 00	
			2	1
Female crimp FC contacts				
Bandoliered contacts (approx. 2,500 pieces)	1	09 06 000 6484		09 06 000 6474
	2	09 06 000 6481		09 06 000 6471
	3	09 06 000 6482		09 06 000 6472
Bandoliered contacts (approx. 250 pieces)	1	09 06 000 7484		09 06 000 7474
	2	09 06 000 7481		09 06 000 7471
	3	09 06 000 7482		09 06 000 7472
Individual contacts ²⁾	1	09 06 000 8484		09 06 000 8474
	2	09 06 000 8481		09 06 000 8471
	3	09 06 000 8482		09 06 000 8472
Female contacts with solder lugs³⁾ (lockable)				09 06 000 6420
		Wire gauge mm ²	AWG	Insulation ø mm
FC 1	1	0.09 - 0.25	28 - 24	0.7 - 1.5
FC 2	2	0.14 - 0.56	26 - 20	0.8 - 2.0
FC 3	3	0.5 - 1.5	20 - 16	1.6 - 2.8
Identification				
Bandoliered contacts				
Individual contacts				
3.5 + 0.5 mm of insulation is stripped from the wires to be crimped Insertion, removal and crimping tools see chapter 30				


¹⁾ With shroud coding, see also page 02.41

²⁾ Packaging unit 1,000 pieces

³⁾ Solder contacts must not be used together with shell housing A. Special contact surface: 2 µm gold.

Number of contacts

48, 32




Female connectors


DIN Power
to 6 A

Identification	Number of contacts	Contact arrangement	Part No. 3	Performance levels according to IEC 60 603-2. Explanation chapter 00	
				2	1
Female connector with solder pins 3.7 mm ¹⁾	48		09 06 248 7848	09 06 248 6848	09 06 248 2848
	32			09 06 232 6848	09 06 232 2848
	32			09 06 232 6858	09 06 232 2858
Female connector with solder pins 4.5 mm ¹⁾	48		09 06 248 7835	09 06 248 6835	09 06 248 2835
	32			09 06 232 6835	09 06 232 2835
	32			09 06 232 6845	09 06 232 2845

Dimensions



Board drillings
Mounting side




Dimensions in mm

¹⁾ With shroud coding, see also page 02.41

Number of contacts

48, 32




Female connectors

Identification	Number of contacts	Contact arrangement	Part No. 3	Performance levels according to IEC 60 603-2. 2	Explanation chapter 00 1
Female connector with wrap posts 22 mm	48		09 06 248 7821	09 06 248 6821	09 06 248 2821
	32		09 06 232 7821	09 06 232 6821	09 06 232 2821
	32		09 06 232 7831	09 06 232 6831	09 06 232 2831
Female connector with solder lugs open solder lug 	48		09 06 248 7823	09 06 248 6823	09 06 248 2823
	32		09 06 232 7823	09 06 232 6823	09 06 232 2823
	32		09 06 232 7843	09 06 232 6843	09 06 232 2843
Dimensions					
Panel cut out	Dimensions in mm Identification strips for female connectors with wrap posts 09 06 000 9939				



Number of contacts

48, 32



Female connectors

DIN Power
to 6 A



Identification	Number of contacts	Contact arrangement	Part No. 3	Performance levels according to IEC 60 603-2. 2	Explanation chapter 00 1				
Female connector “low profile” with solder pins 3.2 mm	48		09 06 248 7833	09 06 248 6833	09 06 248 2833				
	32			09 06 232 6833					
	32			09 06 232 6893					
Female connector “low profile” with solder pins 4.5 mm	48		09 06 248 7834	09 06 248 6834	09 06 248 2834				
	32			09 06 232 6834					
	32		09 06 232 7894	09 06 232 6894	09 06 232 2894				
Female connector with press-in pins	Part Nos. and variants see chapter 04								
Dimensions	<table><tr><td>a</td><td rowspan="3">Solder pins</td></tr><tr><td>3.2</td></tr><tr><td>4.5</td></tr></table>					a	Solder pins	3.2	4.5
a	Solder pins								
3.2									
4.5									
Board drillings Mounting side									

Dimensions in mm

Dimensions in mm

Number of contacts

48, 32




Female connectors

Identification	Number of contacts	Contact arrangement	Part No. 3	Performance levels according to IEC 60 603-2. Explanation chapter 00	
				2	1
Female connector with angled solder pins 1 x 1 mm	48		performance level 3 or special gold plating on request	09 06 248 6826	performance level 1 or special gold plating on request
	32			09 06 232 6826	
	48			09 06 248 6836	
	32			09 06 232 6846	
	32			09 06 232 6836	
Dimensions					
Fixing bracket		Metal	09 06 000 9912 ¹⁾	for version	
		Plastic	09 06 000 9975 ¹⁾	for version	
Board drillings Mounting side					
Dimensions in mm					

DIN Power
to 6 A

Number of contacts

64, 16




Universal adaptors

DIN Power
to 6 A

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Universal adaptor utilising crimp contacts crimp contacts see page 02.29	4 x 4	09 06 016 3301		
	16 x 1	09 06 016 3302		
	16 x 4	09 06 064 3302		
Panel cut out				

max. 9




Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately	9	09 06 209 3201	Technical drawing of the female connector 09 06 209 3201. The front view shows a rectangular body with a central circular feature. Dimensions include a total width of 27.5 ± 0.1, a central width of 16.6, a height of 8.5, and a base width of 17.9. The side view shows a profile with a maximum height of 12.5, a base width of 14.85, and a total length of 25.1. A callout 'fixing' points to a small feature on the side.	max 12,5 $2 \times 3,81 = 7,62$ 3,81 max 12,8 14,85 max 25,1 8 2,9 10,1 17,9 27,5 ± 0,1 16,6 8,5
Female crimp contacts		see page 02.29	Technical drawing of the female crimp contacts. The side view shows a series of crimp contacts with a total width of 24. Dimensions include a contact width of 5.08, a total width of 24, and a height of 11. A callout 'polarization' points to a feature on the side.	24 5,08 11 2 × 5,08 = 10,16 0,3 z a polarization
Male connector for crimp contacts Order contacts separately	9	09 06 109 3401	Technical drawing of the male connector 09 06 109 3401. The front view shows a rectangular body with a central circular feature. Dimensions include a total width of 28, a central width of 21.5, a height of 11.4 max, and a base width of 18 max. The side view shows a profile with a maximum height of 14.8, a base width of 12.7, and a total length of 29. A callout 'fixing' points to a small feature on the side.	28 21,5 19,1 11,4 max 2,9 3 8,4 18 max 14,8 5,6 2,5 6,9 29 36 12,7 2,8 0,3 5,6 12,7 5,08 2 × 5,08 = 10,16 17,1 24 3,81 2 × 3,81 = 7,62
Male crimp contacts		see page 02.38	Technical drawing of the male crimp contacts. The side view shows a series of crimp contacts with a total width of 24. Dimensions include a contact width of 5.08, a total width of 24, and a height of 11. A callout 'polarization' points to a feature on the side.	24 5,08 11 2 × 5,08 = 10,16 0,3 5,6 12,7 3,81 2 × 3,81 = 7,62 polarization

DIN Power to 6 A

Number of contacts

45



Male connectors


DIN Power
to 6 A

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Male connector 29 angled solder pins 16 cavities for male crimp contacts crimp contacts see page 02.38	45	Performance level 1 acc. to IEC 60 603-2 09 06 145 2971		
Board drillings Mounting side				

1) A special 48 way version with 3 extra angled solder contacts at position 16 (rows d, b, z) can be supplied

Number of contacts

45



Female connectors


Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector				
Female moulding with 21 wrap posts 22 mm	45	Performance level 1 acc. to IEC 60603-2 09 06 045 2871	84,9 10 19,5 13 10 22 12,4 2,9_{+0,3} 5,08 2 × 5,08 = 10,16 Latches Crimp moulding is supplied with the female moulding 90_{+0,1} 2,8_{+0,1} 2d 2b 2z 2 × 3,81 = 7,62 5,08 7 × 5,08 = 35,56 10,16 6 × 5,08 = 30,48 8,17 95 max. 0,3 14,8_{+0,2} Contact arrangement View from termination side	
with 21 solder pins 4.5 mm	45	09 06 045 2875		
Crimp moulding for 24 female crimp contacts		09 06 024 3202		
crimp contacts see page 02.29				
Panel cut out			M 2,5 / $\varnothing$ 2,8 8,2 17 8,2 20,32 85 90_{+0,1} 95,5	
Removal tool for the crimp moulding		09 99 000 0172	20 125	The crimp moulding can be extracted with the help of the removal tool.

DIN Power
to 6 A


Number of contacts

max. 24


Interface connector I



DIN Power
to 6 A


Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Interface connector I for male crimp contacts Order contacts separately	24	09 26 024 3411		

Identification	Identification Wire gauge	Part No.	Performance levels according to IEC 60 603-2. Explanation chapter 00	
			2	1
Male crimp FC contacts				
Bandoliered contacts (approx. 2,500 pieces)	1	09 06 000 9564		09 06 000 9544
	2	09 06 000 9561		09 06 000 9541
	3	09 06 000 9562		09 06 000 9542
Bandoliered contacts (approx. 2 50 pieces)	2			09 06 000 5541
	3			09 06 000 5542
Individual contacts ¹⁾	1	09 06 000 9574		09 06 000 9554
	2	09 06 000 9571		09 06 000 9551
	3	09 06 000 9572		09 06 000 9552
FC 1	1	Wire gauge mm ²	AWG	Insulation ø mm
FC 2	2	0.09 - 0.25	28 - 24	0.7 - 1.5
FC 3	3	0.14 - 0.56	26 - 20	0.8 - 2.0
		0.5 - 1.5	20 - 16	1.6 - 2.8
				Identification
				Bandoliered contacts
				Individual contacts
				3.5 + 0.5 mm of insulation is stripped from the wires to be crimped
				Insertion, removal and crimping tools see chapter 30



¹⁾ Packaging unit 1,000 pieces

max. 24




Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Interface connector U with wrap posts 1 x 1 mm	24	09 26 024 2981		Performance level 1 acc. to IEC 60 603-2
Mounting example				

DIN Power to 6 A

Number of contacts





max. 24



Female connectors

DIN Power
to 6 A

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately see page 02.29	24	09 26 024 3201		
Shell housing A with integrated fixing screws Supplied with: Shell 2x Locking screw 2x Screw M3x10 2x Nut M3 2x Screw BZ 2.9x9.5 2x Cable clamp 1x Tension relief 1x		09 26 024 0401		
Open hood Supplied with: Open hood 1x Locking screw 2x Screw BZ 2.2x9.5 2x Cable tie 1x		09 26 000 9901		

Identification	Part No.	Drawing	Dimensions in mm
Coding system <u>with</u> contact loss	Code pin for types D, E, F, FM, 2F 09 04 000 9908 Removal tool for male contacts 09 99 000 0038	To avoid accidental and incorrect mating of adjacent connectors a coding system is required. The coding is achieved by means of a code pin which is inserted into the selected chamber of the female connector (the contact cavity must be filled with a female contact!). The opposite male contact must be removed with the help of the specially designed tool. 	
Coding system <u>without</u> contact loss with code pin	Code pin 09 06 000 9950 Insertion tool 09 99 000 0103	With the aid of the marked indents between the contact rows of the male connector a hole has to be drilled at the desired position (also see drawing). The code pin can then be inserted into the corresponding cavity of the female connector by means of the insertion tool. This coding system is available only for the types D, E, F and interface connectors I  Mounting example 	
shroud coding Type F	Code key 09 06 001 9919	Insert the code key into one of the keyways of the female connector as shown in the drawing. Break out the corresponding area of the male shroud. Connectors coded this way can only be applied in a minimum rack spacing of 20.32 mm. 	
Tool for breaking out the coding area of the male shroud	09 99 000 0242		

Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

Coding system
without contact loss

Male and
female
connectors


Types
B, C, D and E

see product pages
or
on request

To avoid accidental and incorrect mating of adjacent connectors a coding system is required. This coding system is an integral part of both male and female connectors. A comb with 12 coding pins, which is supplied under a single part number, allows over 900 coding variations. The pins are to be locked into the male and female connectors.

The connectors with the integrated coding facility are supplied for types B, C, D and E and are available for all variants.

Please contact us.



Coding pins

12 pins
on a comb
09 02 000 9928



Mounting example

