



- Document Downloads
- Catalog Page
 - PDF
 - DWF
 - IGS
 - STEP
 - X_B

Female-Female Standoff, Hex, Zinc Clear Chromate with Blue Tint, Brass, #6-32, 0.375" Overall Length

Part ID: **BR6951-0632-0.375-34**

Technical Specifications

Material	Brass	Female Thread	#6-32
Grade	360 (ASTM-B-116, QQ-B-626)	Finish Desc. (Spec)	Zinc Clear Chromate with Blue Tint (ASTM-B633)
(Alloy):	353 (ASTM-B-116)	Compliant To	RoHS, WEEE, REACH, Conflict Minerals
Profile	Hex		
Outside Diameter	1/4"		
Overall Length	0.375"		

Available Finishes	
34 - Zinc Clear Chromate with Blue Tint	▼

Product Description

Standoffs are used to create space between 2 objects in an assembly. Lyn-Tron Standoffs are threaded and available in [Female-Female](#), [Male-Female](#), and [Male-Male](#) Thread Configurations to fasten components together. In the world of Electronic Hardware and Electronic Components, Standoffs are most commonly used on Printed Circuit Boards, Motherboards and Panels. The hex shape allows for greater torquing as the flat sides allow for wrench tightening. Brass is corrosion resistant, nonmagnetic, and easily machinable. Base metal is yellow, but many plating options are available when different colors are required.

Stock and Lead Time

Stock	445	Same Day
Stock to Plate	11,000	1 to 2 weeks
Manufacture Lead Time	11-12	Weeks