



## Rating:

3 to 15A, 125, 250VAC, 50VDC

## Approvals:

UL, CUL, VDE, CE

## Interrupting capacity:

1000 amps

## Insulation Resistance:

100M ohms

## Applications:

Household Appliances  
Transportation  
Marine  
Power Strips  
Medical Equipment  
Audio Visual Equipment  
Power Supplies  
Exercise Equipment  
ROHS Compliant

## Ordering Scheme



### 1 SERIES CTB

### 2 BEZEL COLOR<sup>1</sup> B Black

### 3 ROCKER COLOR<sup>1</sup> B Black

### 4 RATING

|    |       |    |        |    |        |
|----|-------|----|--------|----|--------|
| 03 | 3 amp | 08 | 8 amp  | 14 | 14 amp |
| 04 | 4 amp | 09 | 9 amp  | 15 | 15 amp |
| 05 | 5 amp | 10 | 10 amp |    |        |
| 06 | 6 amp | 12 | 12 amp |    |        |
| 07 | 7 amp | 13 | 13 amp |    |        |


### 5 PANEL THICKNESS

blank fits standard thickness of .032 – .062  
B fits .070 – .110 panel thickness

#### Notes:

1 Additional colors available. Consult factory.

## Time Delay




### CORRECTION FACTOR<sup>1</sup>

|      |        |
|------|--------|
| 0°C  | x .67  |
| 10°C | x .72  |
| 15°C | x .83  |
| 18°C | x .87  |
| 25°C | x 1.00 |
| 32°C | x 1.05 |
| 40°C | x 1.18 |
| 50°C | x 1.33 |
| 60°C | x 1.67 |

#### Notes:

1 To adjust the breaker rating for ambient temperature, multiply the breaker rating by the factor. (ex: 5A rating x .850 = 4.25A. Select 4A rating.)

## Dimensional Specifications: in. [mm]



RECOMMENDED PANEL THICKNESS:  
.032 - .062 [.81-1.57]

#### Notes:

All dimensions are in inches [millimeters]. Tolerance  $\pm 0.005$  [.127] unless otherwise specified. Breaker must hold 100% of rated current and must trip at 150% and above, within the time limits shown in curve. Trip times specified at 25° ambient with no preloading.

\*Manufacturer reserves the right to change product specification without prior notice.