

1-1565692-4 Product Details

Share Print Email



1-1565692-4

TE Internal Number: 1-1565692-4
Active

View 3D PDF

Memory Sockets

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Socket Type = Memory Card
- Socket Style = SO DIMM
- Gold Flash Contact Plating, Mating Area, Material
- 200 Positions
- DRAM Type = Double Data Rate (DDR)

View all Features

Quick Links

- ▶ Check Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- [DDR1 & DDR2 SODIMM SOCKET 0.6mm PITCH 200POS LOW PRO...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [DDR S.O.DIMM Socket 200 Positions](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version G1)
- [3D Model](#) (IGES, Version G1)
- [3D Model](#) (STEP, Version G1)

List all Documents

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Socket Style](#) = SO DIMM
- [DRAM Type](#) = Double Data Rate (DDR)
- PCB Mount Style = Surface Mount
- [Module Orientation](#) = Right Angle
- Profile = Low

Mechanical Attachment:

- Keying = Reverse

Electrical Characteristics:

- [DRAM Voltage](#) = 1.8 V

Termination Features:

- Solder Tail Contact Plating = Gold Flash

Body Features:

- Socket Type = Memory Card
- [Number of Positions](#) = 200
- [Row-to-Row Spacing \(mm \[in\]\)](#) = 5.60 [0.220]
- [Centerline \(mm \[in\]\)](#) = 0.60 [0.024]
- [Number of Rows](#) = Dual
- Ejector Type = Locking
- [Ejector Location](#) = Both Ends
- [Number of Keys](#) = 1
- Latch Material = Stainless Steel
- Latch Plating = Tin
- Boss = Without
- Mount Type = Printed Circuit Board

Contact Features:

- Contact Plating, Mating Area, Material = Gold Flash
- Contact Base Material = Copper Alloy

Housing Features:

- Housing Material = High Temperature Thermoplastic
- Housing Color = Black
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Stack Height (mm [in]) = 4.00 [0.157]
- [Insertion Style](#) = Cam-In
- [Center Key \(mm \[in\]\)](#) = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Operation/Application:

- Application Type = DDR SDRAM

Packaging Features:

- Packaging Method = Semi-Hard Tray Assembly
- Packaging Quantity = 20

Other:

- Brand = AMP

Corporate Information

Who We Are
Investors
News Room
Supplier Portal
Careers

Quick Links

Check Distributor Inventory
Cross Reference
Find Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Search Knowledge Base
Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

