

TOSHIBA TRANSISTOR SILICON NPN EPITAXIAL PLANAR TYPE


2SC4245

TV TUNER, UHF MIXER APPLICATIONS.
VHF~UHF BAND RF AMPLIFIER APPLICATIONS.

MAXIMUM RATINGS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector-Base Voltage	V _{CBO}	30	V
Collector-Emitter Voltage	V _{CEO}	15	V
Emitter-Base Voltage	V _{EBO}	3	V
Collector Current	I _C	50	mA
Base Current	I _B	25	mA
Collector Power Dissipation	P _C	100	mW
Junction Temperature	T _j	125	°C
Storage Temperature Range	T _{stg}	-55~125	°C

Unit in mm




ELECTRICAL CHARACTERISTICS (Ta = 25°C)

Weight : 0.006g

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current	I _{CBO}	V _{CB} =30V, I _E =0	—	—	0.1	μA
Emitter Cut-off Current	I _{EBO}	V _{EB} =2V, I _C =0	—	—	1.0	μA
Collector-Emitter Breakdown Voltage	V _{(BR)CEO}	I _C =1mA, I _B =0	15	—	—	V
DC Current Gain	h _{FE}	V _{CE} =10V, I _C =5mA	40	100	200	—
Reverse Transfer Capacitance	C _{re}	V _{CB} =10V, I _E =0, f=1MHz	—	0.6	0.9	pF
Transition Frequency	f _T	V _{CE} =10V, I _C =2mA	1500	2400	—	MHz
Conversion Gain	G _{ce}	V _{CC} =10V, I _C =2mA, f=800MHz	12	17	—	dB
Noise Figure	NF	f _L =830MHz (+2dBm) (Fig.1)	—	8	13	dB


Marking

Type Name



961001EAA2

● TOSHIBA is continually working to improve the quality and the reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to observe standards of safety, and to avoid situations in which a malfunction or failure of a TOSHIBA product could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent products specifications. Also, please keep in mind the precautions and conditions set forth in the TOSHIBA Semiconductor Reliability Handbook.









- $L_1 \sim L_4$: $\phi 0.8\text{mm}$ SILVER PLATED COPPER WIRE
 L_5 : COIL WITH CORE SCN-5948①-③ TOKO OR EQUIVALENT
 L_6 : $\phi 0.2\text{mm}$ COPPER WIRE 10T 5mm I_D
 C_1 : AIR TRIMMER TTA23A100 MURATA MFC. Co., LTD. OR EQUIVALENT


Fig.1 800MHz G_{ce} , NF TEST CIRCUIT

961001EAA2'


- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.




S_{11e}
 $V_{CE}=10V$
 $I_C=2mA$
 $T_a=25^{\circ}C$
(UNIT : Ω)



S_{12e}
 $V_{CE}=10V$
 $I_C=2mA$
 $T_a=25^{\circ}C$



S_{21e}
 $V_{CE}=10V$
 $I_C=2mA$
 $T_a=25^{\circ}C$



S_{22e}
 $V_{CE}=10V$
 $I_C=2mA$
 $T_a=25^{\circ}C$
(UNIT : Ω)

