






PRODUCT NUMBER

SEE SHEET 2



spec ref *				dr Peng-Bing Fu		2013/04/25		projection		MM		size A3		scale 3:2	
tolerance std ASME Y14.5				TOLERANCES UNLESS OTHERWISE SPECIFIED				eng Xie Bob		2013/05/21				ecn no -	
chr -		-		appr Pei-Ming Zheng		2013/05/21		product family PwrBlade+						rel level Released	
surface 		linear		0.X ±0.5				title 3HDP+1LP+24S+1LP+3HDP RA STB HEADER				dwg no 10106262-6206001		rev A	
		0.XX ±0.25													
		0.XXX ±0.10													
ASME Y14.5		angular 0° ±2°		www.fci.com		cat. no.				Product - Customer Drw				sheet 1 of 3	

1

2

3

4

A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



Copyright FCI.

dr	Peng-Bing Fu	2013/04/25	projection	MM	size	scale
eng	Xie Bob	2013/05/21			A3	3:2
chr	-	-			ecn no	-
appr	Pei-Ming Zheng	2013/05/21	product family	PwrBlade+	rel level	Released
www.fci.com		cat. no.	3HDP+1LP+24S+1LP+3HDP RA STB HEADER		dwg no	rev
					10106262-6206001	A
			Product - Customer Drw			sheet 3 of 3

2

3

PDS: Rev :A

STATUS:Released

Printed: May 22, 2013