


SDP8407

Silicon Phototransistor

FEATURES

- End-looking plastic package
- 135° (nominal) acceptance angle
- Low profile for design flexibility
- Mechanically and spectrally matched to SEP8507 infrared emitting diode




INFRA-16.TIF

DESCRIPTION

The SDP8407 is an NPN silicon phototransistor molded in an end-looking black plastic package. The chip is positioned to accept radiation from the top of the package. Lead lengths are staggered to provide a simple method of polarity identification.

OUTLINE DIMENSIONS in inches (mm)

Tolerance	3 plc decimals	±0.008(0.20)
	2 plc decimals	±0.020(0.51)



DIM_018.ds4

SDP8407


Silicon Phototransistor

ELECTRICAL CHARACTERISTICS (25°C unless otherwise noted)						
PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Light Current SDP8407-001	I_L	0.10			mA	$V_{CE}=5\text{ V}$ $H=1\text{ mW/cm}^2$ (1)
Collector Dark Current	I_{CEO}			100	nA	$V_{CE}=10\text{ V}$, $H=0$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	30			V	$I_C=100\text{ }\mu\text{A}$
Emitter-Collector Breakdown Voltage	$V_{(BR)ECO}$	5.0			V	$I_E=100\text{ }\mu\text{A}$
Collector-Emitter Saturation Voltage	$V_{CE(SAT)}$			0.4	V	$I_C=10\text{ }\mu\text{A}$ $H=1\text{ mW/cm}^2$
Angular Response (2)	$\varnothing$		135		degr.	$I_F=\text{Constant}$
Rise And Fall Time	t_r, t_f		15		μs	$V_{CC}=5\text{ V}$, $I_L=1\text{ mA}$ $R_L=1000\text{ }\Omega$

Notes
1. The radiation source is an IRED with a peak wavelength of 935 nm.
2. Angular response is defined as the total included angle between the half sensitivity points.

ABSOLUTE MAXIMUM RATINGS	
(25°C Free-Air Temperature unless otherwise noted)	
Collector-Emitter Voltage	30 V
Emitter-Collector Voltage	5 V
Power Dissipation	100 mW (1)
Operating Temperature Range	-40°C to 85°C
Storage Temperature Range	-40°C to 85°C
Soldering Temperature (5 sec)	240°C

Notes
1. Derate linearly from 25°C free-air temperature at the rate of 0.66 mW/°C.



Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

Honeywell

SDP8407

Silicon Phototransistor

SWITCHING TIME TEST CIRCUIT




Fig. 1 Responsivity vs Angular Displacement





Fig. 3 Dark Current vs Temperature



All Performance Curves Show Typical Values

SWITCHING WAVEFORM




Fig. 2 Collector Current vs Ambient Temperature





Fig. 4 Spectral Responsivity



SDP8407

Silicon Phototransistor



Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

Honeywell