







FCIconnect.com

Copyright FCI

PRODUCT NO

SEE TABLE



mat'l. code				surface		tolerance		projection		product family			
-				ISO 1302		ISO 406 ISO 1101				MOD JACK			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title			
A	V91919	BKB	9/13/99		angles	linear	.X±.3/.01			NET JACK II, RJ45 THRU HOLE			
B	V92061	LP	10/20/99				.XX±.13/.05			SNAP PEG ASSEMBLY			
C	V12718	LP	1/22/02	0'±2'			.XXX±.051/.00020			scale 1:1			
D	M05-0074	ERE	04/22/05	dr	B. BAHN	8/3/99			dwg no		sheet 1 of 5 size		
E	M06-0224	ERE	06/12/06	enrg	B. BRUBAKER	8/3/99			98518		A3		
					chr	B. BRUBAKER 8/3/99							
					appd	B. BRUBAKER 8/3/99							
sheet		revision		E	E	E	E	E					
index		sheet		1	2	3	4	5					
				4					5				


form: A3

PRODUCT NO


SEE TABLE

13.97 [0.550]

13.97 [0.550]


 $\Phi .30 [.012] \textcircled{M} A B C$


FOR PORT NO. 4,6,8


 $\Phi .30 [.012] \textcircled{M} A B C$


FOR 2-PORT

VIEW B

(CENTER PEG OMITTED FOR CLARITY)



VIEW C



VIEW D

SCALE: 2/1

TYP FOR ALL GROUND SPRINGS

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406		MOD JACK
ISO 1101				tolerances unless otherwise specified			title
ltr	ecn	no	dr	date	angles	linear	
E					0°±2'	linear	
							NET JACK II, RJ45 THRU HOLE
							SNAP PEG ASSEMBLY
							dwg no
							sheet 2 of 5 size
							98518 A3
							type
							Product Customer Drawing
sheet	revision						
index	sheet	1					

form: A3

1

2

3

4


5

6

PRODUCT NO.	NO. OF PORTS	DIM A $\begin{smallmatrix} +.60[.024] \\ -.00[.000] \end{smallmatrix}$	DIM B	DIM C $\begin{smallmatrix} \pm.10 \\ [\pm.004] \end{smallmatrix}$	DIM D $\begin{smallmatrix} \pm.15 \\ [\pm.006] \end{smallmatrix}$	DIM E $\begin{smallmatrix} \pm.13 \\ [\pm.005] \end{smallmatrix}$
98518-52YXXX	2	31.68 [1.247]	13.97 [0.550]	12.70 [0.500]	25.40 [1.000]	32.11 [1.264]
98518-52YXXXLF						
98518-54YXXX	4	59.62 [2.347]	41.91 [1.650]	26.67 [1.050]	53.34 [2.100]	60.05 [2.364]
98518-54YXXXLF						
98518-56YXXX	6	87.56 [3.447]	69.85 [2.750]	40.64 [1.600]	81.28 [3.200]	87.99 [3.464]
98518-56YXXXLF						
98518-58YXXX	8	115.50 [4.547]	97.79 [3.850]	54.61 [2.150]	109.22 [4.300]	115.93 [4.564]
98518-58YXXXLF						

NETJACK MAGNETICS
OPTIONS CODE-XXX
SEE GES-12-020

SPRING OPTION Y	DESCRIPTION (SEE SHEET 5 FOR OPTIONAL VIEWS)
1	SPRING ON TOP,BOTTOM AND BOTH SIDES
2	NO SPRINGS
3	SPRINGS ON TOP AND BOTTOM
4	SPRINGS ON TOP,BOTTOM AND 1 PER SIDE (STAGGERED)
5	SAME AS OPTION 4 EXCEPT OPPOSITE STAGGER



NOTES:

- HOUSING MATL: HIGH TEMP. THERMOPLASTIC, COLOR BLACK, UL94V-0.
- CONTACT MATL: COPPER ALLOY
MATING AREA PLATING: Au OVER Ni., (SEE TABLE).
SOLDER AREA PLATING: 2.54uM/100u" MIN TIN LEAD OVER Ni.
LEAD FREE OPTION:
SOLDER AREA PLATING: 2.54uM/100u" MIN PURE TIN OVER Ni.
- SHIELDING MAT'L: TIN PLATED COPPER ALLOY.
- ALL DIMENSIONS IN MILLIMETERS AND INCHES.
- SEE SHEET 5 FOR GROUND TAB CONFIGURATION.
- CENTER PEG FOR 8 PORT ONLY.
- LF SUFFIX AT THE END OF PART NUMBERS IS LEAD FREE.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302 ✓	ISO 406 ISO 1101	MM/INCH	MOD JACK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
E					angles linear		NET JACK II, RJ45 THRU HOLE
					0°±2'	scale 1:1	SNAP PEG ASSEMBLY
							dwg no
					dr B. BAHN 8/3/99		sheet 3 of 5 size
					enrg B. BRUBAKER 8/3/99		98518 A3
					chr B. BRUBAKER 8/3/99		
					appd B. BRUBAKER 8/3/99		type Product Customer Drawing
sheet	revision						
index	sheet	1					

form: A3






FCIconnect.com

Copyright FCI

PRODUCT NO

SEE TABLE

RECOMMENDED P.C.B LAYOUT
AS VIEWED FROM TOP SIDE (COMPONENT SIDE)VIEW C
SCALE 2/1
TYPICAL FOOTPRINT


mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406 ISO 1101		MOD JACK			
ltr	ecr	no	dr	date	tolerances unless otherwise specified		title			
E					angles	linear	NET JACK II, RJ45 THRU HOLE			
					0°±2'		SNAP PEG ASSEMBLY			
							dwg no			
					dr	B. BAHN	8/3/99	sheet 4 of 5 size		
					enr	B. BRUBAKER	8/3/99	98518		A3
					chr	B. BRUBAKER	8/3/99			
					app	B. BRUBAKER	8/3/99	type		Product Customer Drawing
sheet	revision									
index	sheet	1								

form: A3


PRODUCT NO

SEE TABLE


SPRING TAB CONFIGURATION OPTION Y




SPRING OPTION 1




SPRING OPTION 4



SPRING OPTION 2



SPRING OPTION 5



SPRING OPTION 3

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302 ✓	ISO 406 ISO 1101		MOD JACK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	 scale 1:1 	title
E					angles linear		NET JACK II, RJ45 THRU HOLE
					0°±2'		SNAP PEG ASSEMBLY
							dwg no
					dr B. BAHN 8/3/99		sheet 5 of 5 size
					enrg B. BRUBAKER 8/3/99		98518 A3
					chr B. BRUBAKER 8/3/99		type Product Customer Drawing
					appd B. BRUBAKER 8/3/99		
sheet	revision						
index	sheet	1					

form: A3

1

2

3

4

5

6