



SMD Power Inductor



CDRH3D23/HP




Dimension - [mm]



Land pattern and Schematics - [mm]



(1.2 μ H~8.2 μ H)



(10.0 μ H~47.0 μ H)

Description

- Ferrite drum core construction.
- Magnetically shielded.
- L $\times$ W $\times$ H: 3.92 $\times$ 3.92 $\times$ 2.5 mm Max.
- Product weight: 112mg(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: -40 $^{\circ}$ C~+105 $^{\circ}$ C (including coil's self temperature rise)
- Storage temperature range: -40 $^{\circ}$ C~+105 $^{\circ}$ C
- Solder reflow temperature: 260 $^{\circ}$ C peak.

Packaging


- Carrier tape and reel packaging
- 7.0" diameter reel
- 500pcs per reel

Applications

- Ideally used in Mobilephone, PDA, MP3, DSC/DVC, etc. as DC-DC converter inductors.

SMD Power Inductor

CDRH3D23/HP



Electrical Characteristics

Part Name	Stamp	Inductance (μ H) [within] ※1	D.C.R (m Ω) Max. (Typ.) (at 20°C)	Saturation Current (A) ※2		Temperature Rise Current (A) ※3
				at 20°C	at 105°C	
CDRH3D23HPNP-1R2PC	<u>B</u>	$1.2 \pm 25\%$	40.4(32.3)	3.52	3.00	2.55
CDRH3D23HPNP-2R2PC	<u>E</u>	$2.2 \pm 25\%$	50.3(40.2)	2.6	2.24	2.25
CDRH3D23HPNP-2R7PC	<u>F</u>	$2.7 \pm 25\%$	62.3(49.8)	2.4	2.08	2.0
CDRH3D23HPNP-3R3PC	<u>G</u>	$3.3 \pm 25\%$	70.0(56.0)	2.2	1.9	1.85
CDRH3D23HPNP-4R7PC	<u>J</u>	$4.7 \pm 25\%$	95.5(76.4)	1.84	1.57	1.60
CDRH3D23HPNP-5R6PC	<u>K</u>	$5.6 \pm 25\%$	102(81.2)	1.66	1.44	1.50
CDRH3D23HPNP-6R8PC	<u>L</u>	$6.8 \pm 25\%$	136(109)	1.52	1.30	1.30
CDRH3D23HPNP-8R2PC	<u>N</u>	$8.2 \pm 25\%$	145(116)	1.36	1.18	1.25
CDRH3D23HPNP-100MC	A	$10 \pm 20\%$	198(158)	1.28	1.08	1.02
CDRH3D23HPNP-120MC	B	$12 \pm 20\%$	249(199)	1.14	0.97	0.95
CDRH3D23HPNP-150MC	C	$15 \pm 20\%$	276(221)	1.02	0.88	0.90
CDRH3D23HPNP-220MC	E	$22 \pm 20\%$	383(306)	0.80	0.65	0.70
CDRH3D23HPNP-330MC	G	$33 \pm 20\%$	555(444)	0.68	0.58	0.58
CDRH3D23HPNP-470MC	J	$47 \pm 20\%$	798(638)	0.56	0.48	0.45

※1. Inductance measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 70% of it's nominal value.


※3. Temperature rise current: The value of D.C. current when the temperature rise is $\Delta t=40^\circ\text{C}$ ($T_a=20^\circ\text{C}$).

SMD Power Inductor CDRH3D23/HP



Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) — ΔT





SMD Power Inductor CDRH3D23/HP




Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) — ΔT




Solder Reflow Condition

Heat Endurance



Temperature Chart



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com

Chicago

Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com